

Eaton 3BR1224L125R

Catalog Number: 3BR1224L125R

Eaton BR main lug loadcenter, No feed-thru lugs, includes BREQS125 hold-down screw, Main lug, 125 A, C1r, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 24 Circuits, 12 Spaces, Four-wire, Three-phase, 208 Y/120, 240 V, #6-2/0 AWG Cu/Al

General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	3BR1224L125R
UPC	Product Length/Depth
786676441452	5.19 in
Product Height	Product Width
21 in	14.31 in
Product Weight	Warranty
24 lb	10 year
Certifications	Catalog Notes
UL 50 UL 67	Suitable for use as service equipment when no more than 6 main disconnecting means are provided or when not used as lighting & appliance panelboard. Has notch for brhdk125 hold-down kit.



Product specifications

Number of spaces

12

Special features

No feed-thru lugs, includes BREQS125 hold-down screw

Interrupt rating

10 kAIC

Phase

Three-phase

Wire size

#6-2/0 AWG Cu/Al

Bus material

Aluminum

Main circuit breaker

BR

Enclosure

NEMA 3R

Amperage Rating

125 A

Enclosure material

Metallic

Type

Main lug

Cover

Cover included

Used with

Type BR 1-inch breakers

NEMA rating

NEMA 3R

Number of wires

4

Number of circuits

24

Voltage rating

208Y/120, 240V

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

[Type BR 3-Phase Loadcenters](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, OUTDOOR NEMA 3R, 120/240 VAC, 3 PHASE](#)

Specifications and datasheets

[Eaton Specification Sheet - 3BR1224L125R](#)

[3-Phase Loadcenter Program](#)

Box size

C1R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)