

Eaton 3BR1836L150

Catalog Number: 3BR1836L150

Eaton BR main lug loadcenter, No feed-thru lugs, Main lug, 150 A, C2, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, BWH, Combination, 36 Circuits, 18 Spaces, Four-wire, Three-phase, Type BR 1-inch breakers, 208 Y/120, 240 V, #1 AWG-300 kcmil Cu/Al

General specifications

Product Name	Eaton BR main lug loadcenter	Catalog Number	3BR1836L150
UPC	786676441551	Product Length/Depth	3.88 in
Product Height	4.5 in	Product Width	14.31 in
Product Weight	22.5 lb	Warranty	10 year
Certifications	UL 67 UL 50	Catalog Notes	Suitable for use as service equipment when no more than 6 main disconnecting means are provided or when not used as lighting & appliance panelboard

Product specifications

Number of spaces

18

Special features

No feed-thru lugs

Interrupt rating

25 kAIC

Phase

Three-phase

Wire size

#1 AWG-300 kcmil Cu/Al

Bus material

Aluminum

Main circuit breaker

BWH

Enclosure

NEMA 1

Amperage Rating

150 A

Mounting

Combination

Enclosure material

Metallic

Type

Main lug

Cover

Cover included

Used with

Type BR 1-inch breakers

NEMA rating

NEMA 1

Number of wires

4

Number of circuits

36

Resources

Brochures

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, INDOOR
NEMA 1, 120/240 VAC, 3 PHASE

Specifications and datasheets

3-Phase Loadcenter Program

Eaton Specification Sheet - 3BR1836L150

Voltage rating

208Y/120, 240V

Box size

C2



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)