

Eaton 3BR2442L150R

Catalog Number: 3BR2442L150R

Eaton BR main lug loadcenter, No feed-thru lugs, Main lug, 150 A, D1R, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, BWH, NEMA 3R, 42 Circuits, 24 Spaces, Four-wire, Three-phase, Type BR 1-inch breakers, 208 Y/120, 240 V, #1 AWG-300 kcmil Cu/Al



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	3BR2442L150R
UPC	Product Length/Depth
786676441759	5.19 in
Product Height	Product Width
21 in	14.31 in
Product Weight	Warranty
32 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Special features

No feed-thru lugs

Type

Main lug

Amperage Rating

150 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Number of circuits

42

Number of spaces

24

Phase

Three-phase

Used with

Type BR 1-inch breakers

Voltage rating

208Y/120, 240V

Wire size

#1 AWG-300 kcmil Cu/Al

Box size

D1R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

NEMA rating

NEMA 3R

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR 3-Phase Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, OUTDOOR NEMA 3R, 120/240 VAC, 3 PHASE

Specifications and datasheets

3-Phase Loadcenter Program

Eaton Specification Sheet - 3BR2442L150R

Number of wires

4



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)