



Metal Raceway






HBL2400 and HBL2400D Series

Metal Raceway, Device Boxes, Elbows and Tees

HBL2400 Series	Description	Color	Catalog Number
	Undivided Base and Cover Packed 50 ft. (15m) per carton, 5 ft. (1.5m) lengths.	Ivory	HBL2400BCIV A: 60.00" (1,524.00) B: 1.91" (48.51) C: .88" (22.40)





HBL2400 Series Base and Cover	Description	Color	Catalog Number	HBL2400D Series Base and Cover	Description	Color	Catalog Number
	10 Ft. Base, Undivided Packed 100 ft. (30.5m) per carton, 10 ft. (3m) lengths.	Ivory	HBL2400B10IV A: 120.00" (3,048.00) B: 1.91" (48.51)		5 Ft. Cover Packed 50 ft. (15m) per carton, 5 ft. (1.5m) lengths.	Ivory	HBL2400CIV A: 60.00" (1,524.00) B: 1.89" (48.00)
	5 Ft. Base, Undivided Packed 50 ft. (15m) per carton, 5 ft. (1.5m) lengths.	Ivory	HBL2400BIV A: 60.00" (1,524.00) B: 1.91" (48.51)				
	10 Ft. Base, Divided Packed 100 ft. (30.5m) per carton, 10 ft. (3m) lengths.	Ivory	HBL2400BDIV A: 120.00" (3,048.00) B: 1.91" (48.51)				



Standard	Extra Deep	Description	Color	Type	1-Gang	2-Gang
		Device Box For deep switches and receptacles. Base has one 1/2 in. trade size KO and rectangular KO for extension to wall box.	Ivory Ivory	Divided Undivided	— HBL2448IV A: 4.54" (115.32) B: 2.82" (71.63) C: 1.75" (44.45)	— HBL24482IV A: 4.54" (115.32) B: 4.64" (117.86) C: 1.75" (44.45)
		Device Box For deep switches and receptacles. Base has one 1/2 in. trade size KO and rectangular KO for extension to wall box (undivided box pictured).	Ivory Ivory	Divided Undivided	HBL2444DIV HBL2444IV A: 4.54" (115.32) B: 2.82" (71.63) C: 2.75" (69.85)	HBL2444D2AIV HBL24442IV A: 4.54" (115.32) B: 4.64" (117.86) C: 2.75" (69.85)

Elbows and Tees	Description	Color	Type	Catalog Number	Description	Color	Type	Catalog Number
	Internal Elbow Bend Radius For inside surfaces at right angles, requiring a 1.5 in. (38.10) bend radius. Suitable for Category 5, 5e, 6 and 6a applications.	Ivory Ivory	Divided Undivided	HBL2417DFOIV* HBL2417IV** A: 1.91" (48.51) B: 3.60" (91.30)	External Elbow Bend Radius For right angle turns around external corners. Suitable for Category 5, 5e, 6 and 6a applications.	Ivory Ivory	Divided Undivided	HBL2418DFOIV* HBL2418IV** A: 1.91" (48.51) B: 3.83" (97.28)
	90° Flat Elbow Bend Radius For right angle turns on same surface. Suitable for Category 5, 5e, 6 and 6a applications.	Ivory Ivory	Divided Undivided	HBL2411DFOIV* HBL2411IV** A: 6.00" (152.40) B: 5.00" (127.00) C: .90" (22.86)	Tee Fitting Bend Radius For branches at right angles. Suitable for Category 5, 5e, 6 and 6a applications.	Ivory Ivory	Divided Undivided	HBL2415DFOIV* HBL2415IV** A: 7.30" (185.42) B: 4.99" (126.75) C: 1.44" (36.58)



Note: * HBL2401DC couplings included.
** HBL2401C couplings included.





Metal Raceway






HBL2400 and HBL2400D Series

Metal Raceway, Device Boxes, Elbows and Tees

HBL2400 Series	Description	Color	Catalog Number
	Undivided Base and Cover Packed 50 ft. (15m) per carton, 5 ft. (1.5m) lengths.	Ivory	HBL2400BCIV A: 60.00" (1,524.00) B: 1.91" (48.51) C: .88" (22.40)





HBL2400 Series Base and Cover	Description	Color	Catalog Number	HBL2400D Series Base and Cover	Description	Color	Catalog Number
	10 Ft. Base, Undivided Packed 100 ft. (30.5m) per carton, 10 ft. (3m) lengths.	Ivory	HBL2400B10IV A: 120.00" (3,048.00) B: 1.91" (48.51)		5 Ft. Cover Packed 50 ft. (15m) per carton, 5 ft. (1.5m) lengths.	Ivory	HBL2400CIV A: 60.00" (1,524.00) B: 1.89" (48.00)
	5 Ft. Base, Undivided Packed 50 ft. (15m) per carton, 5 ft. (1.5m) lengths.	Ivory	HBL2400BIV A: 60.00" (1,524.00) B: 1.91" (48.51)				
	10 Ft. Base, Divided Packed 100 ft. (30.5m) per carton, 10 ft. (3m) lengths.	Ivory	HBL2400BDIV A: 120.00" (3,048.00) B: 1.91" (48.51)				



	Description	Color	Type	1-Gang	2-Gang
Standard	Device Box For deep switches and receptacles. Base has one 1/2 in. trade size KO and rectangular KO for extension to wall box.	Ivory	Divided	—	—
		Ivory	Undivided	HBL2448IV A: 4.54" (115.32) B: 2.82" (71.63) C: 1.75" (44.45)	HBL24482IV A: 4.54" (115.32) B: 4.64" (117.86) C: 1.75" (44.45)
Extra Deep	Device Box For deep switches and receptacles. Base has one 1/2 in. trade size KO and rectangular KO for extension to wall box (undivided box pictured).	Ivory	Divided	HBL2444DIV	HBL2444D2AIV
		Ivory	Undivided	HBL2444IV A: 4.54" (115.32) B: 2.82" (71.63) C: 2.75" (69.85)	HBL24442IV A: 4.54" (115.32) B: 4.64" (117.86) C: 2.75" (69.85)

	Description	Color	Type	Catalog Number	Description	Color	Type	Catalog Number
Elbows and Tees	Internal Elbow Bend Radius For inside surfaces at right angles, requiring a 1.5 in. (38.10) bend radius. Suitable for Category 5, 5e, 6 and 6a applications.	Ivory	Divided	HBL2417DFOIV*	External Elbow Bend Radius For right angle turns around external corners. Suitable for Category 5, 5e, 6 and 6a applications.	Ivory	Divided	HBL2418DFOIV*
		Ivory	Undivided	HBL2417IV** A: 1.91" (48.51) B: 3.60" (91.30)		Ivory	Undivided	HBL2418IV** A: 1.91" (48.51) B: 3.83" (97.28)
	90° Flat Elbow Bend Radius For right angle turns on same surface. Suitable for Category 5, 5e, 6 and 6a applications.	Ivory	Divided	HBL2411DFOIV*	Tee Fitting Bend Radius For branches at right angles. Suitable for Category 5, 5e, 6 and 6a applications.	Ivory	Divided	HBL2415DFOIV*
		Ivory	Undivided	HBL2411IV** A: 6.00" (152.40) B: 5.00" (127.00) C: .90" (22.86)		Ivory	Undivided	HBL2415IV** A: 7.30" (185.42) B: 4.99" (126.75) C: 1.44" (36.58)



Note: * HBL2401DC couplings included.
** HBL2401C couplings included.

