

---

# 40083

---

F96T12 CW SUPREME/ALTO (PK X 15)

---



**Application:** Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

**Base:** Single Pin (Fa8)

**Coating:** Copolymer

**Color Temperature:** 4100K

**Diameter:** 1.50 IN

**Lamp Type:** Fluorescent

**Mean Design Lumens:** 4250

**Package Weight:** 22.65 L

**Shape:** T

**Type:** Straight Linear Fluorescent Lamp

**Wattage:** 75.0 W

**Average Life Hours:** 12000

**Bulb:** T12

**Color:** Cool White

**CRI:** 89

**Initial Lumens:** 5000

**Length:** 96.00 IN

**Package (LxWxH):** 96.25 IN x 8.75 IN x 5.25 IN

**Pack By:** 15

**Special Features:** Shatter-Resistant

**UPC:** 726585400836

ULEPH,ROHS,NSF Non-Food Zone,NSF Splash Zone

---

# 40083

---

F96T12 CW SUPREME/ALTO (PK X 15)

---



**Application:** Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

**Average Life Hours:** 12000

**Base:** Single Pin (Fa8)

**Bulb:** T12

**Coating:** Copolymer

**Color:** Cool White

**Color Temperature:** 4100K

**CRI:** 89

**Diameter:** 1.50 IN

**Initial Lumens:** 5000

**Lamp Type:** Fluorescent

**Length:** 96.00 IN

**Mean Design Lumens:** 4250

**Package (LxWxH):** 96.25 IN x 8.75 IN x 5.25 IN

**Package Weight:** 22.65 L

**Pack By:** 15

**Shape:** T

**Special Features:** Shatter-Resistant

**Type:** Straight Linear Fluorescent Lamp

**UPC:** 726585400836

**Wattage:** 75.0 W

ULEPH,ROHS,NSF Non-Food Zone,NSF Splash Zone