



412	6"	7.830	.450
411	5"	6.487	.450
410	4"	5.320	.275
409	3 1/2"	4.700	.275
408	3"	4.165	.250
407	2 1/2"	3.470	.250
406	2"	2.890	.250
405	1 1/2"	2.376	.187
404	1 1/4"	2.080	.187
403	1"	1.730	.160
402	3/4"	1.383	.140
401	1/2"	1.125	.130
PART NO.	TRADE SIZE	"A"	"B"