




GE
Lighting

25781 - 40R16/CD

GE soft white 40 watt R16 floodlight 1-pack

- Use original GE's Soft White when you need a light without glare and harsh shadows.
- Replace ordinary light bulbs with GE Flood and Spotlight in all your track and recessed lighting fixtures.
- 2500K soft white light appearance
- Estimated yearly energy costs \$4.82 based on 3 hours per day \$0.11 per kWh
- GE soft white indoor spotlights provide warm, pleasing everyday light without harsh glares and shadows. These bulbs' funnel shape and reflective coating help direct light where it is needed better than a standard incandescent bulb
- Lasts 1.4 years based on 3 hours per day usage
- 280 lumens providing subtle, reassuring™ light
- R16 indoor floodlight with medium base for use in directional fixtures such as recessed can lighting



GENERAL CHARACTERISTICS

Lamp Type	Incandescent - Reflector
Bulb	R16
Base	Medium Screw (E26)
Filament	CC-6
Rated Life	1500.0 hrs
Bulb Material	Soft glass
Primary Application	Indoor Spotlight

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	225.0
Color Temperature	2500.0 K

ELECTRICAL CHARACTERISTICS


Wattage	40.0
Voltage	120.0

DIMENSIONS

Maximum Overall Length (MOL)	3.3700 in(85.6 mm)
Bulb Diameter (DIA)	2.000 in(50.8 mm)

PRODUCT INFORMATION

Product Code	25781
Description	40R16/CD
Standard Package	BUNDLE
Standard Package GTIN	30043168257818
Standard Package Quantity	30
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	30
UPC	043168257817



CAUTIONS & WARNINGS

Warning

- Unexpected lamp rupture may cause injury, fire, or property damage
 - Avoid direct water, liquid or metal contact.
- Risk of Fire
 - Keep combustible materials away from lamp.