

Product Specifications



4" x 100' Pipe Wrap (10 Mil)

Part Number 410

Category Number 5420

UPC 781002281429

Pipe Wrap is a polyvinyl chloride film tape coated with a rubber resin adhesive that protects pipes, joints, conduit and couplings for overhead or direct burial applications. It is corrosion and puncture resistant.



Physical Characteristics

Type	Pipe Wrap
Size	4" x 100'
Length (ft)	100'
Width (in)	4"
Thickness (mil)	10 mil
Material	Polyvinyl Chloride
Backing Material	Plasticized PVC
Finish	Matte
Color	Black

Packaging Details

Standard Qty	1
Master Qty	12
Price Per	1
Package Length	4.10
Package Width	4.20
Package Height	3.90
Package Weight	2.35

Performance Data

Tensile Strength (lb/in)	20 lb/in
Elongation	2
Applications	Pipe, Joints, Conduit and Couplings for Overhead or Direct Burial Applications
Temperature Range	32°F to 140°F
Dielectric Strength	550 V/mil
Voltage Rating (V)	600V
Resists	Corrosion, Abrasion, Punctures, UV, Moisture, Fungus
Adhesion to Steel	20 oz/in
Adhesion to Backing	20 oz/in
UV Resistance	Yes
Special Features	Lead Free, Weather Resistant, Direct Burial Approved, Excellent Conformability, Individual Cello Wrapped

Certifications

RoHS Compliant	Yes
----------------	-----