



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

IMAGE
COMING
SOON

41874 8' 42W Led T8 41K DBL End FA8/R17D 2 4' Sections *Sylvania-Ledvance*

Catalog Number	41874
Manufacturer	Sylvania-Ledvance
Description	8FT Ledlescent Direct Wire Ballast Free Type B Led T8, Glass With Frosted Shatter Resistant Pet Coating, 42W, 120 277V, 80 Cri, 5000 Lumens, 4100K, 50000 HRS Life. 2 PC Snap Fit Design. Changeable Single Pin and RDC Base, Dimmable
Weight per unit	0.8820 (lbs/each)
Product Category	Lighting

Features

lumens	5,040
Voltage	120.00 - 277.00 V

Descriptions

Description	8' 42W LED T8 41K DBL END FA8/R17D 2 4' SECTIONS
extra long description	SYL LED42T8HOL96-2FGP841BF/41874 LE
Long Description	8ft LEDlescent Direct Wire Ballast Free Type B LED T8, Glass with frosted shatter resistant PET coating, 42W, 120 277V, 80 CRI, 5000 Lumens, 4100K, 50000 Hrs life. 2 pc Snap Fit design. Changeable single pin and RDC base, dimmable
Product Type	LED42T8HOL96 2FGP841BF 10/CS 10/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135418747
Manufacturers Part Number	LED42T8HOL96-2FGP841BF/41874
UPC	046135418747

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Package	10
Weight Per each	0.882