



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

IMAGE
COMING
SOON

41878 12W Led T8 48" 3K/35/41K/5K/65K DBL/SNGL End 1800L *Sylvania-Ledvance*

Catalog Number	41878
Manufacturer	Sylvania-Ledvance
Description	4FT Led T8 Ledlescenttm (UI Type B), Frosted Pet Shatter Resistant Glass, 12W, 120 277V, 82 Cri, 1800 Lumens, 3000K/3500K/4100K/5000K/6500K CCT Selectable, 50, 000 HRS Life, Dimmable
Weight per unit	0.4410 (lbs/each)
Product Category	Lighting

Features

Lamp Type	LED BALLAST-FREE
-----------	------------------

Descriptions

Description	12W LED T8 48" 3K/35/41K/5K/65K DBL/SNGL END 1800L
extra long description	SYL LED12T8L48FGDIM8SC12BF/41878 LE
Long Description	4ft LED T8 LEDlescentTM (UL Type B), Frosted PET shatter resistant glass, 12W, 120 277V, 82 CRI, 1800 lumens,3000K/3500K/4100K/5000K/6500K CCT Selectable, 50,000 hrs life, Dimmable
Product Type	LED12T8L48FGDIM8SC12BF 25/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135418785
Manufacturers Part Number	LED12T8L48FGDIM8SC12BF/41878
UPC	046135418785

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	25
Weight Per each	0.441