ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
7520 Eastgate Blvd Suite 100
37122-0000, TN Mt. Juliet
Phone: 615-257-4146
Fax: 615-257-4147



420 9.5" Tongue & Groove

Channellock , Inc.

Catalog Number	420
Manufacturer	Channellock , Inc.
Description	Groove Joint Plier, 1.5 In Cutting Capacity, C1080 High Carbon Steel Cutting Material, Plastic Grip Handle Material, Channellock Blue (Handle), 9.5 In Overall Length, 1.12 In Jaw Length, 0.47 In Jaw Width, 1.57 In Shank Length, 13 Pieces
Weight per unit	0.8700 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

Features

Handle Type	CHANNELLOCK BLUE® grips for comfort
Jaw Opening	1.5 in in
Material	CHANNELLOCK® uses high-carbon C1080 steel for superior performance on the job and electronic coating for ultimate rust prevention

Dimensions and Weight

Length	9-1/2"
Size	9.5" Tongue & Groove

Descriptions

Construction	Patented reinforcing edge minimizes stress breakage
Description	9.5" TONGUE & GROOVE

Manufacturer Information

Brand	CHANNELLOCK
GTIN	00025582300676
UPC	025582300676

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Tongue & Groove, Pump Plier, Water Plier, Tools

Availability

Manufacturer Status	Inactive

Packaging

Carton	1
Package	5
Weight Per each	0.87

Uses, Certifications, and Standards

Application	Mechanical/Home Repair/Auto/Plumbing