


## Steel - Rigid/Liquidtight Transition - Raintight

### Images



### Application

For creating a Liquidtight/Raintight Connection between 2 different Raceways: 3/4" Rigid Conduit (GRC &&& IMC) and 3/4" Liquidtight Flexible Metallic Conduit (LFMC). Suitable for use in wet locations. Concrete Tight

### Product Information

Material: Malleable Iron

Finish: Zinc Coated

### Certifications & Codes:

CSA File Number: cULus

Federal Specification Number: A-A-50553A

NEMA Standard: FB-1

UL File Number: E9391

UL Standard: 514B

UNSPSC: 39131707

[Download Photo Image](#)

[Download Dimensional Image](#)

Dimension A in Inches: 7/8

Dimension B in Inches: 3/4

Dimension C in Inches: 1-5/8

**Catalog ID:** 4371-LT

**UPC Number:** 78174720371

**Description:** Combination Coupling for transitioning between 3/4" Liquidtight Flexible Metallic Conduit (LFMC) and 3/4" Rigid Steel Conduit. NPSM Threads on Hub. Malleable Iron Body with Steel Ferrule

**Application:** For creating a Liquidtight/Raintight Connection between 2 different Raceways: 3/4" Rigid Conduit (GRC &&& IMC) and 3/4" Liquidtight Flexible Metallic Conduit (LFMC). Suitable for use in wet locations. Concrete Tight

**Trade Size:** 3/4"

**Std Pkg Qty:** 50

**Unit Qty:** 10