

# Eaton 4424 HS

Catalog Number: 4424 HS

Eaton B-Line series wiring trough, 4" height, 24" length, 4" width, HS wireway, Thru holes, 7 top knockouts, 7 bottom knockouts, Hinged cover, NEMA 1, Steel, Hinged, ANSI 61 gray, 16 gauge

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series wiring trough	4424 HS
<b>UPC</b>	<b>Product Length/Depth</b>
782051477931	24 in
<b>Product Height</b>	<b>Product Width</b>
4 in	4 in
<b>Product Weight</b>	<b>Certifications</b>
6.716 lb	CSA C22.2. UL Listed

## Material/finish

### Material thickness

16 gauge

### Finish color

ANSI 61 gray

## Model

### Closure type

Hinged

### Mounting method

Thru holes

### Special features

Cover is secured to the body with plated screws

### Type

HS wireway

## Resources

### Catalogs

[EnviroShield Wireway Flyer](#)

### Specifications and datasheets

[Eaton Specification Sheet - 4424 HS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)