

4592250	6"	8	8.643	1.358
4592	6"	8	8.253	1.358
4591250	5"	8	7.639	.990
4591	5"	8	7.249	.990
459250	4"	8	6.672	.992
459	4"	8	6.282	.992
458250	3 1/2"	8	6.443	.969
458	3 1/2"	8	5.783	.969
457250	3"	8	5.200	.970
457	3"	8	4.810	.970
456250	2 1/2"	8	5.042	.942
456	2 1/2"	8	4.652	.942
455100	2"	11 1/2	3.927	.715
455	2"	11 1/2	3.604	.715
454100	1 1/2"	11 1/2	3.453	.715
454	1 1/2"	11 1/2	3.130	.715
453100	1 1/4"	11 1/2	3.214	.644
453	1 1/4"	11 1/2	2.734	.644
452	1"	11 1/2	2.384	.576
451	3/4"	14	2.109	.482
450	1/2"	14	1.896	.458
PART NO.	TRADE SIZE	THDS/ INCH	"A"	"B"

