

15 Amp NEMA L615 Single Receptacle

4560



Receptacle Single 15amp 250volt Turnlok

features & benefits



- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

specifications

General Info

Type: Single, Receptacles

Listing Agencies/Third Party Information

UL Listing No: 498
UL Standard: Yes
UN SPS C: 39121403

Dimensions

Depth U S: .922"
Diameter U S: 1.375"
Height U S: 3.281"

Technical Information

Amps: 15 Amp
NEMA Configuration Number: L615
Volts: 250V
Volts A C: 250

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant