

4592250	6"	8	8.643	1.358	7.050	2.320
4592	6"	8	8.253	1.358	7.050	1.865
4591250	5"	8	7.639	.990	6.035	2.206
4591	5"	8	7.249	.990	6.035	1.865
459250	4"	8	6.672	.992	5.040	2.203
459	4"	8	6.282	.992	5.040	1.725
458250	3 1/2"	8	6.443	.969	4.545	2.211
458	3 1/2"	8	5.783	.969	4.545	1.741
457250	3"	8	5.200	.970	4.022	2.223
457	3"	8	4.810	.970	4.022	1.790
456250	2 1/2"	8	5.042	.942	3.425	2.204
456	2 1/2"	8	4.652	.942	3.425	1.735
455100	2"	11 1/2	3.927	.715	2.665	1.496
455	2"	11 1/2	3.604	.715	2.665	1.385
454100	1 1/2"	11 1/2	3.453	.715	2.184	1.496
454	1 1/2"	11 1/2	3.130	.715	2.184	1.385
453100	1 1/4"	11 1/2	3.214	.644	1.944	1.496
453	1 1/4"	11 1/2	2.734	.644	1.944	1.496
452	1"	11 1/2	2.384	.576	1.607	1.070
451	3/4"	14	2.109	.482	1.333	1.070
450	1/2"	14	1.896	.458	1.114	1.070
PART NO.	TRADE SIZE	THDS/ INCH	"A"	"B"	"C"	"D"

