ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1135 Butler Road
77573-0000, TX League City
Phone: 281-833-5333
Fax: 281-833-5334



46400 Thermo-Shrink Uf Splice Kit, 14-8 Awg

Ideal

Catalog Number	46400
Manufacturer	Ideal
Description	Uf Splice Kit, 600 V Ac, 8 In Overall Length, 1.1 In Outside Diameter, 0 °C Operating Temperature, +105 °C Operating Temperature, 0.2 LB
Weight per unit	0.2000 (lbs/each)
Product Category	Wire

Features

Cable Size	14 - 8

Descriptions

Description	THERMO-SHRINK UF SPLICE KIT, 14-8 AWG
extra long description	IDEAL 46-400 UF SPLICE KIT
Features	Direct burial rated14/3 with and without ground thru 8/3 without ground, UF?cable rangeStretcher kit repairs a 7 in. to 10 in. section damaged or destroyed by a trencher600V Maximum, 105°C ratingMeets the requirements of the 2002 NEC?Code 110-14(b) and UL486DUV resistant
Special Features	Features: Direct Burial Rated; Heavy-Wall Heat Shrinkable Tubing - TS-46 Irradiated Cross-Linked Polyolefin With 3:1 Standard Shrink Ratio; Adhesive Liner Provides Complete Insulation And Protection; Simple One-Piece Design Saves Time And Money

Manufacturer Information

Brand	Ideal
GTIN	00783250464005
UPC	783250464005

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	UF Splice Kits

Packaging

Carton	1
Weight Per each	0.2

Uses, Certifications, and Standards

standard	RoHS