
46558

F32T8 ADV850/ALTO (PK X 30)



Application: Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

Base: Medium Bi-Pin (G13)

Coating: Copolymer

Color Temperature: 5000K

Diameter: 1.00 IN

Lamp Type: Fluorescent

Mean Design Lumens: 3025

Package Weight: 15.40 L

Shape: T

Type: Straight Linear Fluorescent Lamp

Wattage: 32.0 W

Average Life Hours: 36000

Bulb: T8

Color: ADV850

CRI: 82

Initial Lumens: 3100

Length: 48.00 IN

Package (LxWxH): 49.80 IN x 6.50 IN x 7.90 IN

Pack By: 30

Special Features: Shatter-Resistant

UPC: 726585465583

ULEPH,UL 2007A,ROHS,NSF Non-Food Zone,NSF Splash Zone

46558

F32T8 ADV850/ALTO (PK X 30)



Application: Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

Base: Medium Bi-Pin (G13)

Coating: Copolymer

Color Temperature: 5000K

Diameter: 1.00 IN

Lamp Type: Fluorescent

Mean Design Lumens: 3025

Package Weight: 15.40 L

Shape: T

Type: Straight Linear Fluorescent Lamp

Wattage: 32.0 W

Average Life Hours: 36000

Bulb: T8

Color: ADV850

CRI: 82

Initial Lumens: 3100

Length: 48.00 IN

Package (LxWxH): 49.80 IN x 6.50 IN x 7.90 IN

Pack By: 30

Special Features: Shatter-Resistant

UPC: 726585465583

ULEPH,UL 2007A,ROHS,NSF Non-Food Zone,NSF Splash Zone