

Lampholder Adapters & Accessories

Keyless Switch
Medium Base
660W, 250V/AC

FEATURES

- One piece screwshell with porcelain base.



1054

Socket Extensions

660W 250V/AC

Description	Color	Catalog No.
Phenolic Medium Base Socket, Extends 1.38" (34.9mm)	Black	☐ 1054

   Listed to UL496, file no. E15055; CSA certified to C22.2, no. 43; NOM certified

Lampholder Adapters & Accessories

Lamp Guards


FEATURES

- 1.25" (31.8mm) clamp fits metal shell lampholders.
- 1.50" (38.1mm) clamp fits ceiling lampholders, sign and scoreboard Attachon lampholders.
- 1465 is high-strength impact-resistant thermoplastic.
- Easy-open guard permits relamping without removing guard.



469

Lamp Guards

Description	Color	Catalog No.	
Metal Lamp Guard with 1.25" (31.8mm) Collar, 100W Bulb Max.	Steel	☐ 469A	•
Metal Lamp Guard with 1.50" (38.1mm) Collar, 100W Bulb Max.	Steel	☐ 469B	•
Plastic Lamp Guard with Adjustable Collar, 200W Bulb Max.	Yellow	☐ 1465Y	

Dimensional Information: B-65

Specification Information: Please visit
www.cooperwiringdevices.com

 **NAFTA Compliant:** See page F-21