



**M18 REDLITHIUM™**  
**THE WORLD'S FIRST & ONLY 18V**  
**HIGH DEMAND™ 9.0 BATTERY**

[Learn More](#)

Swap Banner



## 9" 18 TPI The Torch™ Double Duty Upgrade™ Ice Hardened™ SAWZALL® Blades (5 Pk)

48-00-4788



### What's Included

(1) 9" 18 TPI The Torch™ Double Duty Upgrade™ Ice Hardened™ SAWZALL® Blades (5 Pk) (48-00-4788)

### Where to Buy

- Shop Online
- Find Local

### Features

- Optimized tooth design providing 2X more life than our previous generation SAWZALL® blades
- Tough Neck™ ribs strengthen the blade tang and minimize breakage
- Grid Iron™ honeycomb pattern increases blade rigidity to resist blade buckling.

### Specifications

<b>TPI</b>	18
<b>Length</b>	9.09"
<b>Profile</b>	Demo
<b>Pack Qty</b>	5 Pack
<b>Shank</b>	1/2" Universal
<b>Material</b>	Rigid Conduit Strut

### Overview

The Torch™ metal-cutting blades with the Double Duty Upgrade™ feature a tooth form optimized for the longest life and maximum durability. Tough Neck™ is engineered to protect against tang breakage and delivers the strongest SAWZALL® blade tang on the market. Grid Iron™ features a stamped honeycomb pattern throughout the body of the blade that greatly increases the rigidity of the blade, making it the stiffest metal cutting SAWZALL® blade on the market. Ice Hardened blades are cryogenically treated for up to 50% longer life. These blades are ideal for making tough, straight cuts.

### Model Options

Item/Cat #	TPI	Length	Profile	Pack Qty
------------	-----	--------	---------	----------

48-00-4712	10	6.06"	Demo	5 Pack	Shop Online Find Local
48-00-4713	10	9.09"	Demo	5 Pack	Shop Online Find Local
48-00-4782	14	6.06"	Demo	5 Pack	Shop Online Find Local
48-00-4784	18	6.06"	Demo	5 Pack	Shop Online Find Local
48-00-4787	14	9.09"	Demo	5 Pack	Shop Online Find Local
48-00-4788	18	9.09"	Demo	5 Pack	Shop Online Find Local
48-01-8712	10	6.06"	Demo	50 Pack	Shop Online Find Local
48-01-8713	10	9.09"	Demo	50 Pack	Shop Online Find Local
48-01-8782	14	6.06"	Demo	50 Pack	Shop Online Find Local
48-01-8784	18	6.06"	Demo	50 Pack	Shop Online Find Local
48-01-8787	14	9.09"	Demo	50 Pack	Shop Online Find Local
48-01-8788	18	9.09"	Demo	50 Pack	Shop Online Find Local
48-01-9712	10	6.06"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-9713	10	9.09"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-9782	14	6.06"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-9784	18	6.06"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-9787	14	9.09"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-9788	18	9.09"	Demo	100 Pack (Bulk)	Shop Online Find Local





**M18 REDLITHIUM™**  
**THE WORLD'S FIRST & ONLY 18V**  
**HIGH DEMAND™ 9.0 BATTERY**

[Learn More](#)

Swap Banner



## 9" 18 TPI The Torch™ Double Duty Upgrade™ Ice Hardened™ SAWZALL® Blades (5 Pk)

48-00-4788



### What's Included

(1) 9" 18 TPI The Torch™ Double Duty Upgrade™ Ice Hardened™ SAWZALL® Blades (5 Pk) (48-00-4788)

### Where to Buy

- Shop Online
- Find Local

### Features

- Optimized tooth design providing 2X more life than our previous generation SAWZALL® blades
- Tough Neck™ ribs strengthen the blade tang and minimize breakage
- Grid Iron™ honeycomb pattern increases blade rigidity to resist blade buckling.

### Specifications

<b>TPI</b>	18
<b>Length</b>	9.09"
<b>Profile</b>	Demo
<b>Pack Qty</b>	5 Pack
<b>Shank</b>	1/2" Universal
<b>Material</b>	Rigid Conduit Strut

### Overview

The Torch™ metal-cutting blades with the Double Duty Upgrade™ feature a tooth form optimized for the longest life and maximum durability. Tough Neck™ is engineered to protect against tang breakage and delivers the strongest SAWZALL® blade tang on the market. Grid Iron™ features a honeycomb pattern throughout the body of the blade that greatly increases the rigidity of the blade, making it the stiffest metal cutting SAWZALL® blade on the market. Ice Hardened blades are cryogenically treated for up to 50% longer life. These blades are ideal for making tough, straight cuts.

### Model Options

Item/Cat #	TPI	Length	Profile	Pack Qty
------------	-----	--------	---------	----------

48-00-4712	10	6.06"	Demo	5 Pack	Shop Online Find Local
48-00-4713	10	9.09"	Demo	5 Pack	Shop Online Find Local
48-00-4782	14	6.06"	Demo	5 Pack	Shop Online Find Local
48-00-4784	18	6.06"	Demo	5 Pack	Shop Online Find Local
48-00-4787	14	9.09"	Demo	5 Pack	Shop Online Find Local
48-00-4788	18	9.09"	Demo	5 Pack	Shop Online Find Local
48-01-8712	10	6.06"	Demo	50 Pack	Shop Online Find Local
48-01-8713	10	9.09"	Demo	50 Pack	Shop Online Find Local
48-01-8782	14	6.06"	Demo	50 Pack	Shop Online Find Local
48-01-8784	18	6.06"	Demo	50 Pack	Shop Online Find Local
48-01-8787	14	9.09"	Demo	50 Pack	Shop Online Find Local
48-01-8788	18	9.09"	Demo	50 Pack	Shop Online Find Local
48-01-9712	10	6.06"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-9713	10	9.09"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-9782	14	6.06"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-9784	18	6.06"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-9787	14	9.09"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-9788	18	9.09"	Demo	100 Pack (Bulk)	Shop Online Find Local

