



SDS-PLUS 2CT 1/2" X 4" X 6"

48-20-7471



Where to Buy



Shop Online

Find Local

Features

-
- Enhanced Rebar Guards provide increased durability
-
- Breaker Points lead to faster drilling speeds
-
- Variable Flute for Up to 20% more Holes per Charge in Cordless Rotary Hammers
-
- Centering Tip for exact spot drilling
-
- Wear Mark Indicators to show end of life and when bit no longer meets the ANSI requirement
-
- Reinforced Flutes for minimized vibration and maximum durability
-

Specifications

Pack Qty	1 Pack
Diameter	.5001/2"
Length	6"
Style	SDS-PLUS
Useable Length	4"
Cutter Geometry	2-Cutter
Height	0.5"
Width	0.5"

Overview

Milwaukee® M/2™ 2-Cutter SDS-Plus Rotary Hammer Drill bits are the Most Durable 2-Cutter bits with up to 20% more holes per charge in cordless rotary hammers. The enhanced rebar guards provide increased durability in hard

aggregate and rebar. Breaker Point pulverize the material more effectively resulting in faster drilling speeds. The variable flute allows for maximum debris extraction leading to up 20% more holes per charge in cordless rotary hammer

while making it a very durable bit in corded and cordless rotary hammers. Additionally, M/2™ features a centering tip for exact spot drilling, wear mark indicator indicating when the bit no longer meets ANSI diameter requirements, and a reinforced flute for durability and minimized vibration. The increased life and efficiency of the M/2™ 2-Cutter drill bit line provides the ideal solution in general concrete for cordless and corded rotary hammer users.

Model Options

Item/Cat #	Style	Diameter	Length	Cutter Geometry	Pack Qty	
48-20-7400	SDS-PLUS	.1565/32"	4"	2-Cutter	1 Pack	Shop Online
48-20-7401	SDS-PLUS	.1565/32"	6"	2-Cutter	1 Pack	Shop Online
SDS-PLUS 2CT 3/16" X 2" X 4" 48-20-7410		.1873/16"	4"		1 Pack	Shop Online
48-20-7411	SDS-PLUS	.1873/16"	6"	2-Cutter	1 Pack	Shop Online
48-20-7412	SDS-PLUS	.1873/16"	8"	2-Cutter	1 Pack	Shop Online
48-20-7413	SDS-PLUS	.1873/16"	10"	2-Cutter	1 Pack	Shop Online
48-20-7414	SDS-PLUS	.1873/16"	12"	2-Cutter	1 Pack	Shop Online
48-20-7415	SDS-PLUS	.1873/16"	14"	2-Cutter	1 Pack	Shop Online

48-20-7416	SDS-PLUS	.1873/16"	16"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7421	SDS-PLUS	.2187/32"	6"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7422	SDS-PLUS	.2187/32"	8"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7424	SDS-PLUS	.2187/32"	10"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7425	SDS-PLUS	.2187/32"	14"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7426	SDS-PLUS	.2187/32"	16"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7430	SDS-PLUS	.2501/4"	4"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7431	SDS-PLUS	.2501/4"	6"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7432	SDS-PLUS	.2501/4"	8"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7433	SDS-PLUS	.2501/4"	8"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7533	SDS-PLUS	.2501/4"	8"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼

48-20-7434	SDS-PLUS	.2501/4"	12"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7435	SDS-PLUS	.2501/4"	14"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7436	SDS-PLUS	.2501/4"	16"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7438	SDS-PLUS	.2501/4"	20"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7441	SDS-PLUS	.3125/16"	6"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7444	SDS-PLUS	.3753/8"	12"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7451	SDS-PLUS	.3753/8"	6"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7452	SDS-PLUS	.3753/8"	8"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7453	SDS-PLUS	.3753/8"	10"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7454	SDS-PLUS	.3753/8"	12"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7457	SDS-PLUS	.3753/8"	18"	2-Cutter	1 Pack	Shop Online	▲ ▼

48-20-7459	SDS-PLUS	.3753/8"	24"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7461	SDS-PLUS	.4377/16"	6"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7464	SDS-PLUS	.4377/16"	12"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7467	SDS-PLUS	.4377/16"	18"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7471	SDS-PLUS	.5001/2"	6"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7473	SDS-PLUS	.5001/2"	10"	2-Cutter	1 Pack	Shop Online	▲ ▼
SDS-PLUS 2CT 1/2" X 10" X 12" 48-20-7474	SDS-PLUS	.5001/2"	12"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7477	SDS-PLUS	.5001/2"	18"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7479	SDS-PLUS	.5001/2"	24"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7481	SDS-PLUS	.5629/16"	6"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7484	SDS-PLUS	.5629/16"	12"	2-Cutter	1 Pack	Shop Online	▲ ▼

48-20-7487	SDS-PLUS	.5629/16"	18"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7601	SDS-PLUS	.6255/8"	6"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7602	SDS-PLUS	.6255/8"	8"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7604	SDS-PLUS	.6255/8"	12"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7607	SDS-PLUS	.6255/8"	18"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7609	SDS-PLUS	.6255/8"	24"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7058	SDS-PLUS	.68711/16"	8"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7061	SDS-PLUS	.7503/4"	8"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7063	SDS-PLUS	.7503/4"	10"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7065	SDS-PLUS	.7503/4"	12"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7066	SDS-PLUS	.7503/4"	18"	2-Cutter	1 Pack	Shop Online	▲ ▼

48-20-7067	SDS-PLUS	.7503/4"	24"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7071	SDS-PLUS	.8757/8"	8"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7072	SDS-PLUS	.8757/8"	12"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7075	SDS-PLUS	.8757/8"	18"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7080	SDS-PLUS	1.001"	10"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7085	SDS-PLUS	1.001"	18"	2-Cutter	1 Pack	Shop Online	▲ ▼
48-20-7500	SDS-PLUS	.1565/32"	4"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
48-20-7501	SDS-PLUS	.1565/32"	6"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
48-20-7510	SDS-PLUS	.1873/16"	4"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
48-20-7511	SDS-PLUS	.1873/16"	6"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
48-20-7512	SDS-PLUS	.1873/16"	8"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼

48-20-7513	SDS-PLUS	.1873/16"	10"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
48-20-7514	SDS-PLUS	.1873/16"	12"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
48-20-7515	SDS-PLUS	.1873/16"	14"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
48-20-7516	SDS-PLUS	.1873/16"	16"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
48-20-7521	SDS-PLUS	.2187/32"	6"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
48-20-7522	SDS-PLUS	.2187/32"	8"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
48-20-7524	SDS-PLUS	.2187/32"	10"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
SDS-PLUS 2CT 7/32" X 12" X 14" - BULK (25) 48-20-7525	SDS-PLUS	.2187/32"	14"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
48-20-7526	SDS-PLUS	.2187/32"	16"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
48-20-7530	SDS-PLUS	.2501/4"	4"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
48-20-7531	SDS-PLUS	.2501/4"	6"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼

48-20-7532	SDS-PLUS	.2501/4"	8"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
48-20-7534	SDS-PLUS	.2501/4"	12"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
48-20-7535	SDS-PLUS	.2501/4"	14"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
48-20-7536	SDS-PLUS	.2501/4"	16"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
48-20-7541	SDS-PLUS	.3125/16"	6"	2-Cutter	25 Pack (Bulk)	Shop Online	▲ ▼
48-20-7551	SDS-PLUS	.3753/8"	6"	2-Cutter	20 Pack (Bulk)	Shop Online	▲ ▼
48-20-7554	SDS-PLUS	.3753/8"	12"	2-Cutter	20 Pack (Bulk)	Shop Online	▲ ▼
48-20-7571	SDS-PLUS	.5001/2"	6"	2-Cutter	15 Pack (Bulk)	Shop Online	▲ ▼
48-20-7574	SDS-PLUS	.5001/2"	12"	2-Cutter	15 Pack (Bulk)	Shop Online	▲ ▼
48-20-7702	SDS-PLUS	.6255/8"	8"	2-Cutter	10 Pack (Bulk)	Shop Online	▲ ▼
48-20-7810	SDS-PLUS	.1873/16"	4"	2-Cutter	200 (Bulk)	Shop Online	▲ ▼

48-20-7811	SDS-PLUS	.1873/16"	6"	2-Cutter	200 (Bulk)	Shop Online	▲ ▼
48-20-7830	SDS-PLUS	.2501/4"	4"	2-Cutter	200 (Bulk)	Shop Online	▲ ▼
48-20-7831	SDS-PLUS	.2501/4"	6"	2-Cutter	200 (Bulk)	Shop Online	▲ ▼
48-20-7841	SDS-PLUS	.3125/16"	6"	2-Cutter	150 (BULK)	Shop Online	▲ ▼
48-20-7851	SDS-PLUS	.3753/8"	6"	2-Cutter	125 (Bulk)	Shop Online	▲ ▼
48-20-7871	SDS-PLUS	.5001/2"	6"	2-Cutter	100 Pack (Bulk)	Shop Online	▲ ▼