

# Eaton 483612-SDSS4

Catalog Number: 483612-SDSS4

Eaton B-Line series wall mounted panel enclosure,48" height,12" length,36" width,NEMA 4X,Hinged cover,SDSS4 enclosure,Wall mount,Medium single door,Thru holes,opt. external mounting feet,304 stainless steel,Seamless poured in-place gasket

## General specifications



Product Name	Catalog Number
Eaton B-Line series wall mounted panel enclosure	483612-SDSS4
	UPC
	782051093742

Product Length/Depth	Product Height
12 in	48 in

Product Width	Product Weight
36 in	124.1 lb

### Certifications

UL 50  
CSA C22.2.  
NEMA

## Product specifications

### Special features

Stainless 1/4 turn latches

### Closure type

Hinged

### Finish color

#4 brushed

### Color

Gray

### Wall thickness

14 gauge, 14 gauge

### Material

304 stainless steel

### Mounting method

Wall

### Country of origin

US

### Cover type

Hinged

### Mounting hole details

Thru holes, optional external mounting feet

### NEMA Rating

4X

### Model

SDSS4 enclosure

### Style

Medium single door

## Resources

### Catalogs

[Disconnect Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 483612-SDSS4](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)