



## 10-Piece SHOCKWAVE™ RED HELIX™ Titanium Drill Bit Set

Milwaukee® SHOCKWAVE Impact Duty Titanium Drill Bits with RED HELIX are engineered for impacts and drills. Designed with a Variable Helix with an aggressive 35° Helix Angle which ends at 15°, the Impact Duty Titanium Drill bits with RED HELIX provide Rapid Chip Removal to limit heat buildup to Stay Sharper Longer. The 135° split point tip delivers a precision start and prevents walking for fast, accurate holes. Titanium coating can be used in all drilling applications to give you up to 3X life vs. Black Oxide Drill Bits.

### INCLUDES:

[\(2\) 1/8" \(48-89-4605\)](#)
[\(1\) 9/64" \(48-89-4606\)](#)
[\(1\) 5/32" \(48-89-4607\)](#)  
[\(1\) 11/64" \(48-89-4608\)](#)
[\(1\) 3/16" \(48-89-4609\)](#)
[\(1\) 7/32" \(48-89-4611\)](#)  
[\(1\) 1/4" \(48-89-4613\)](#)
[\(1\) 5/16" \(48-89-4617\)](#)
[\(1\) 3/8" \(48-89-4621\)](#)

### FEATURES:

- SHOCKWAVE Impact Duty, Engineered for Drills and Impacts
- RED HELIX Design for Rapid Chip Removal
- CHIP BREAKER Decreased Heat Buildup
- 135° split point for precision start no walking

### PRODUCT SPECIFICATIONS:

Product Depth (in.)	2.5 in	Product Width (in.)	7 in
Product Height (in.)	7 in		



## 10-Piece SHOCKWAVE™ RED HELIX™ Titanium Drill Bit Set

Milwaukee® SHOCKWAVE Impact Duty Titanium Drill Bits with RED HELIX are engineered for impacts and drills. Designed with a Variable Helix with an aggressive 35° Helix Angle which ends at 15°, the Impact Duty Titanium Drill bits with RED HELIX provide Rapid Chip Removal to limit heat buildup to Stay Sharper Longer. The 135° split point tip delivers a precision start and prevents walking for fast, accurate holes. Titanium coating can be used in all drilling applications to give you up to 3X life vs. Black Oxide Drill Bits.

### INCLUDES:

[\(2\) 1/8" \(48-89-4605\)](#) [\(1\) 9/64" \(48-89-4606\)](#) [\(1\) 5/32" \(48-89-4607\)](#)  
[\(1\) 11/64" \(48-89-4608\)](#) [\(1\) 3/16" \(48-89-4609\)](#) [\(1\) 7/32" \(48-89-4611\)](#)  
[\(1\) 1/4" \(48-89-4613\)](#) [\(1\) 5/16" \(48-89-4617\)](#) [\(1\) 3/8" \(48-89-4621\)](#)

### FEATURES:

- SHOCKWAVE Impact Duty, Engineered for Drills and Impacts
- RED HELIX Design for Rapid Chip Removal
- CHIP BREAKER Decreased Heat Buildup
- 135° split point for precision start no walking

### PRODUCT SPECIFICATIONS:

Product Depth (in.)	2.5 in	Product Width (in.)	7 in
Product Height (in.)	7 in		