



### 4-Piece SHOCKWAVE™ RED HELIX™ Titanium Drill Bit Set

Milwaukee® SHOCKWAVE Impact Duty Titanium Drill Bits with RED HELIX are engineered for impacts and drills. Designed with a Variable Helix with an aggressive 35° Helix Angle which ends at 15°, the Impact Duty Titanium Drill bits with RED HELIX provide Rapid Chip Removal to limit heat buildup to Stay Sharper Longer. The 135° split point tip delivers a precision start and prevents walking for fast, accurate holes. Titanium coating can be used in all drilling applications to give you up to 3X life vs. Black Oxide Drill Bits.

### INCLUDES:

- (1) 1/8 inches (3.2mm)
- (1) 5/32 inches (4.0 mm)
- (1) 3/16 inches (4.8 mm)
- (1) 1/4 inches (6.4 mm)

### FEATURES:

- SHOCKWAVE Impact Duty, Engineered for Drills and Impacts
- RED HELIX Design for Rapid Chip Removal
- CHIP BREAKER Decreased Heat Buildup
- 135° split point for precision start no walking

### PRODUCT SPECIFICATIONS:

Warranty	Limited Lifetime Warranty
----------	---------------------------



### 4-Piece SHOCKWAVE™ RED HELIX™ Titanium Drill Bit Set

Milwaukee® SHOCKWAVE Impact Duty Titanium Drill Bits with RED HELIX are engineered for impacts and drills. Designed with a Variable Helix with an aggressive 35° Helix Angle which ends at 15°, the Impact Duty Titanium Drill bits with RED HELIX provide Rapid Chip Removal to limit heat buildup to Stay Sharper Longer. The 135° split point tip delivers a precision start and prevents walking for fast, accurate holes. Titanium coating can be used in all drilling applications to give you up to 3X life vs. Black Oxide Drill Bits.

### INCLUDES:

- (1) 1/8 inches (3.2mm)
- (1) 5/32 inches (4.0 mm)
- (1) 3/16 inches (4.8 mm)
- (1) 1/4 inches (6.4 mm)

### FEATURES:

- SHOCKWAVE Impact Duty, Engineered for Drills and Impacts
- RED HELIX Design for Rapid Chip Removal
- CHIP BREAKER Decreased Heat Buildup
- 135° split point for precision start no walking

### PRODUCT SPECIFICATIONS:

Warranty

Limited Lifetime Warranty