



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 4SLSTP4040DDUNV 4' 43W Led Strip 40K 4000LM

*Cooper Lighting Solutions*

Catalog Number	4SLSTP4040DDUNV
Manufacturer	Cooper Lighting Solutions
Description	Linear Led Striplight, 120 to 277 V, 0.36 A @120 V;0.15 A @ 277, 44 W, Cold Rolled Steel, White, 4000 K, 80, 50000 H Average Life, Dimmable, Painted, 4760 LM Brightness (Lumens), 46-1/2 In Length, 2-7/16 In Width, 2-7/16 In Height, 4.6 LB
Weight per unit	6.5 (lbs/each)
Product Category	Led Surface Architectural & SP

### Features

amperage rating	0.155 at (277V)
Lamp Type	LED
lumens	4927
Number of Lamps	1
Socket Type	N/A
Wattage	41 W

### Dimensions and Weight

Size	47.813 IN Length 3.813 IN Width 3.625 IN Height
------	---

### Descriptions

Description	4' 43W LED STRIP 40K 4000LM
extra long description	CLS 4SLSTP4040DD-UNV 4FT LINEAR LED

### Manufacturer Information

Brand	METALUX
GTIN	00080083705825
UPC	080083705825

### Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Striplights

### Packaging

Carton	1
Weight Per each	6.5

### Uses, Certifications, and Standards

Mounting	Surface/Pendant/Wall Mount
standard	UL/cULus Listed;CSA Certified