



ADJUSTABLE T-GRID BOX HANGER, 24" T-GRID SPAN

CATALOG NUMBER

512A



FEATURES

Adjustable height allows installation of double deep boxes, speaker cases and emergency light fixtures above T-Grid

Snaps easily onto T-Grid

Hanger comes complete with box mounting clip and screw

PRODUCT ATTRIBUTES

Material: Steel;Spring Steel

Finish: Pregalvanized;nVent CADDY Armour

T-Grid Span: 24

Height: 8" Max

Ultimate Static Load: 20 lb

ADDITIONAL PRODUCT DETAILS

Not to exceed static load without independent wire support to box mounting clip.

Not permitted for paddle fans.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER



ADJUSTABLE T-GRID BOX HANGER, 24" T-GRID SPAN

CATALOG NUMBER

512A



FEATURES

Adjustable height allows installation of double deep boxes, speaker cases and emergency light fixtures above T-Grid

Snaps easily onto T-Grid

Hanger comes complete with box mounting clip and screw

PRODUCT ATTRIBUTES

Material: Steel;Spring Steel

Finish: Pregalvanized;nVent CADDY Armour

T-Grid Span: 24

Height: 8" Max

Ultimate Static Load: 20 lb

ADDITIONAL PRODUCT DETAILS

Not to exceed static load without independent wire support to box mounting clip.

Not permitted for paddle fans.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER