



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



5139RD Wallplate 2G Toggle Nylon STD RD

Eaton Wiring Devices

Catalog Number	5139RD
Manufacturer	Eaton Wiring Devices
Description	Eaton Toggle Wallplate, Red, Toggle Cutout, Nylon, Two- Gang, Standard, Ed Box
Weight per unit	0.0700 (lbs/each)
Product Category	Wall Plates & Covers

Features

dimensions	0.0600 IN X 4.5600 IN X 4.5000 IN
media	Yes

Descriptions

Description	WALLPLATE 2G TOGGLE NYLON STD RD
extra long description	EWD 5139RD-BOX Wallplate 2G Toggle
Features	Eaton's broad offering of wallplates are the final touch for any application and are available in standard size, mid-size and oversize. Upgrade your home with screwless wallplates which provide a clean, seamless look. Choose from a variety of materials, colors, and configurations to match any combination of device and décor. Weather protective covers are available in a wide selection of configurations to maintain the integrity of outdoor devices.
Long Description	Eaton Toggle wallplate, Red, Toggle Cutout, Nylon, Two- gang, Standard, ED Box
Product Type	Wallplate 2G Toggle Nylon STD RD
Special Features	Thermoplastic, std and midi

Manufacturer Information

Brand	Arrow Hart
GTIN	00032664481505
Manufacturers Part Number	5139RD-BOX
UPC	032664481505

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	Toggle wallplate

Packaging

Carton	1
Package	100
Weight Per each	0.07



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other Residential Bldgs &
Facilities - Residential Bldgs & Facilities - Other

standard

cULus Listed,UL Listed,RoHS Compliant,NAFTA