



# Round Weatherproof Cluster Cover, Three 1/2 in. Threaded Outlets, White

By Bell  
Catalog # 5197-1



Round Weatherproof Cluster Cover, Three 1/2 in. Threaded Outlets, White

## Features

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package
- Three hole covers supplied with two closure plugs
- NEMA 3R rated

## General

Color	<ul style="list-style-type: none"> <li>• White</li> <li>• Blanc</li> </ul>
Construction	Metallic
Cover Type	Lampholder/Cluster
Material	Die Cast Aluminum
Number Of Outlets	3
Type	<ul style="list-style-type: none"> <li>• Cover</li> <li>• Cover</li> </ul>
UPC	050169519714

## Dimensions

Actual Depth	1.094 in
Height	4.125 in
Weight	0.198 lb
Width	4.125 in

## Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"> <li>• UL Listed</li> <li>• CSA Certified</li> </ul>
Industry Standard(s)	UL 514A
Nema Rating	NEMA 3R

## Logistics

Carton Quantity	20
Packaging Type	Shrink
Pallet Quantity	3600
Standard Package	20

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Sales Drawings - 5193 series, 5197 series](#)
- [SDS - HCC\\_SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BELL-5197-1-SPEC-EN | REV 1/2024