



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



524DCI2 1-1/2" Ins Screw-In Connector *Bridgeport Fittings*

| | |
|------------------|--|
| Catalog Number | 524DCI2 |
| Manufacturer | Bridgeport Fittings |
| Description | Connector, Screw-In, Zinc Die Cast, 105 Degree C Insulated Throat, Flex Size 1 1/2 Inch |
| Weight per unit | 0.4200 (lbs/each) |
| Product Category | Liquid Tight Fittings |

Features

| | |
|----------------|---------------------|
| angle | 180 Deg |
| Connector Type | Screw-In, Insulated |
| Material | Zinc Die Cast |
| media | Yes |

Material, Color, and Finish

| | |
|--------|--------------|
| Finish | Ball burnish |
|--------|--------------|

Dimensions and Weight

| | |
|------|-------|
| Size | 1-1/2 |
|------|-------|

Descriptions

| | |
|------------------------|--|
| Description | 1-1/2" INS SCREW-IN CONNECTOR |
| extra long description | BPT 524-DCI2 1 1/2" SCREW-IN CONN I |
| Long Description | Connector, Screw-In, Zinc Die Cast, 105 Degree C Insulated Throat, Flex Size 1 1/2 Inch |
| Product Type | 1 1/2" Screw-In Conn Ins |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | Bridgeport Fittings |
| GTIN | 00781747165244 |
| Manufacturers Part Number | 524-DCI2 |
| UPC | 781747165244 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | FLEX & MC FITTINGS |
| Type | CONNECTOR |

Trade Size

| | |
|------------|-------|
| Trade Size | 1-1/2 |
|------------|-------|

Packaging

| | |
|-----------------|------|
| Carton | 5 |
| Package | 50 |
| Weight Per each | 0.42 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------|---|
| Application | Used to connect flexible metal conduit to box or enclosure. |
| standard | UL |
| Temperature Rating | 105°C |