



Powering Business Worldwide

5250BLS

Recp TVSS 15A 125V 2P3W W/Led BL

UPC: 040893627458

Brand Name: Eaton
Sub Brand: ARROW HART
Type: Duplex, Straight Blade
Special Features: Wiring Type Side Wire
Application: Commercial grade
Standard: UL
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 10 AWG
Amperage Rating: 20 Amp
Voltage Rating: 125 Vac
Material: PVC
Color: Black
NEMA Rating: 5-20R
Mounting: Flush
Connection: Screw
Size: 0.82 In Depth X 4.19 In Height
Environmental Conditions: See Spec Sheet
Dielectric Strength: 2000 V
Insulation: PVC
Temperature Rating: -20C to 70C (-4F to 158F)

5250BLSM

Recp TVSS 15A 125V 2P3W W/Led MOD BL

UPC: 032664674020

Brand Name: Eaton
Sub Brand: ARROW HART
Type: Single, Straight Blade
Special Features: Wiring Type Side Wire
Application: Commercial grade
Standard: UL
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 10 AWG
Amperage Rating: 20 Amp
Voltage Rating: 250 Vac
Material: Nylon
Color: Almond
NEMA Rating: 6-20R
Mounting: Flush
Connection: Screw
Size: 0.83 In Depth
Environmental Conditions: See Spec Sheet
Dielectric Strength: 2000 V
Insulation: Nylon
Temperature Rating: -20C to 70C (-4F to 158F)



Powering Business Worldwide

5250VS

Recp TVSS 15A 125V 2P3W W/Led IV

UPC: 040893627472

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Heavy Duty

Special Features: Wiring Type Side Wire

Application: Commercial

Voltage Rating: 120/277 Vac

Amperage Rating: 15 Amp

Number Of Poles: 1

Connection: Screw

Actuator: Compact Toggle

Color: Almond

Contact Configuration: Switches

Size: 0.87 In Depth X 1.13 In Width X 2.38 Back X 3.28 Screw to Screw

Mounting: Wall

Operating Temperature: -40 To 65 DegC

5250VSM

Recp TVSS 15A 125V 2P3W W/Led MOD IV

UPC: 032664674044

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Heavy Duty

Special Features: Wiring Type Side Wire

Application: Commercial

Voltage Rating: 120/277 Vac

Amperage Rating: 15 Amp

Number Of Poles: 1

Connection: Screw

Actuator: Compact Toggle

Color: Black

Contact Configuration: Switches

Size: 0.87 In Depth X 1.13 In Width X 2.38 Back X 3.28 Screw to Screw

Mounting: Wall

Operating Temperature: -40 To 65 DegC



Powering Business Worldwide

5250WS

Recp TVSS 15A 125V 2P3W W/Led WH

UPC: 040893641546

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Heavy Duty

Special Features: 3-Way, Wiring Type Side Wire

Application: Commercial

Voltage Rating: 120/277 Vac

Amperage Rating: 15 Amp

Connection: Screw

Actuator: Compact Toggle

Color: Black

Contact Configuration: Switches

Size: 0.87 In Depth X 1.13 In Width X 2.38 Back X 3.28 Screw to Screw

Mounting: Wall

Operating Temperature: '-40 To 65 DegC

5250WSM

Recp TVSS 15A 125V 2P3W W/Led MOD WH

UPC: 032664674051

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Heavy Duty

Special Features: Wiring Type Side Wire

Application: Commercial

Voltage Rating: 120/277 Vac

Amperage Rating: 20 Amp

Number Of Poles: 1

Connection: Screw

Actuator: Compact Toggle

Color: Almond

Contact Configuration: Switches

Size: 0.87 In Depth X 1.13 In Width X 2.38 Back X 3.28 Screw to Screw

Mounting: Wall

Operating Temperature: '-40 To 65 DegC

5250GYSM

Recp TVSS 15A 125V 2P3W W/Led MOD BL

UPC: 032664674037

Brand Name: Eaton

Sub Brand: Eaton

Type: Duplex, Straight Blade

Special Features: Standard Grade, Flush Fitting, Temperature Rating -40 To 90 Deg C, Opening Configuration 2.1563 In Diameter

Application: Industrial

Standard: UL

Amperage Rating: 15 Amp