

# Specification Grade Surge Protective Duplex Receptacle, White

5262WSP



Extra Heavy-Duty Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back & Side Wire, 15amp 125volt, White.

## features & benefits

- **Solid-state LED monitor** has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place.
- **LED Indication:** Steady green = protected, Flashing red = not protected, OFF = no power to unit
- **Audible alarm alert** of MOV damage. Alarm able to be turned On/Off.
- **Wrap-around steel strap** for structural integrity. Auto-ground is standard, for easier installation.
- **Impact-resistant thermoplastic exterior** resists impacts and scrapes.
- **Triple-wipe, copper-alloy contacts** for superior, more dependable connection.
- **External screw-pressure-plate back and side wire terminals including ground with external back wire clamps (exclusive)** accept #14 - #10 AWG copper or copper-clad, solid or stranded conductors. External pressure plate feature allows two conductors to be terminated by a single screw.
- **Thermal protection in 3 modes. 3 17mm dual pack MOVs absorb up to 340 Joules** of excess energy in each leg (L-N, L-G, N-G) with 24,000 amp current handling capability for full, equal and symmetrical protection. Protection response time in less than one nanosecond.

## specifications

### General Info

Color: White  
Type: Duplex  
Duty: Extra Heavy Duty  
Special Features: Audible Alarm with LED Monitor, Isolated Ground

### **Listing Agencies/Third Party Information**

CSA Listing Info: No  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: Yes  
Fed Spec Number: WC596  
UL Listing No: No  
UN SPS C: 39121406  
UR: No

### **Dimensions**

Depth U S: 1.225" (Behind Strap)  
Height U S: 3.82"  
Width U S: 1.750"

### **Technical Information**

Amps: 15 Amp  
Volts: 125V  
Volts A C: 125  
Grade Type: Specification

### **Buy American Act Compliance**

Country of Origin: CHINA  
Buy American Act Status: No