



Industrial grade straight blade devices

Product description

2-pole, 3-wire grounding
15A, 125V/AC
NEMA 5-15



AH5266



AH5969BK



AH5278C



AH5278

Industrial grade plugs & connectors



Rating A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
15	125	5-15	Ultra grip straight body	0.33-0.66" (8.3-16.7mm)	BK & W	<input type="checkbox"/> AH5266	<input type="checkbox"/> AH5269	•	•
			Ultra grip straight body	0.33-0.66" (8.3-16.7mm)	BK	<input type="checkbox"/> AH5266BK	<input type="checkbox"/> AH5269BK	•	•
			Safety grip angled body	0.33-0.66" (8.3-16.7mm)	BK & W	<input type="checkbox"/> AH5266A	—	•	•
			Quick grip straight body	0.22-0.66" (5.6-16.7mm)	BK	<input type="checkbox"/> AH5965BK	<input type="checkbox"/> AH5969BK	•	
			Quick grip straight body	0.22-0.66" (5.6-16.7mm)	Y	<input type="checkbox"/> AH5965Y	<input type="checkbox"/> AH5969Y	•	
			Auto grip straight body	0.33-0.66" (8.3-16.7mm)	BK & W	<input type="checkbox"/> 5266N	<input type="checkbox"/> 5269N	•	•

Industrial grade flanged inlets & outlets



Rating A	V/AC	NEMA	Description	Color	Inlet catalog no.	Outlet catalog no.	
15	125	5-15	Nylon construction, back wire	BK & W	<input type="checkbox"/> AH5278C [†]	<input type="checkbox"/> AH5279C*	•
			Metal shell, back wire	Steel	<input type="checkbox"/> AH5278 [‡]	<input type="checkbox"/> AH5246	•

* UL and CSA Listed, [†] Fed Spec certified, [‡]Only NOM spec

Industrial grade dimensional information: B-16, B-17

Specification information:

Safety grip industrial plugs & connectors: B-24
Quick grip plugs & connectors: B-24
Auto grip industrial plugs & connectors: B-24
Industrial flanged inlets & Flanged outlets: B-25

Color information:

BK (Black), W (White), Y (Yellow)



Compliances, specifications and availability are subject to change without notice.



Indicates NAFTA compliant - Page Q-32

RoHS compliant - Page Q-32

Industrial grade straight blade devices

Product description

2-pole, 3-wire grounding
15A, 125V/AC
NEMA 5-15



AH5266



AH5969BK



AH5278C



AH5278

Industrial grade plugs & connectors



Rating A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
15	125	5-15	Ultra grip straight body	0.33-0.66" (8.3-16.7mm)	BK & W	<input type="checkbox"/> AH5266	<input type="checkbox"/> AH5269	•	•
			Ultra grip straight body	0.33-0.66" (8.3-16.7mm)	BK	<input type="checkbox"/> AH5266BK	<input type="checkbox"/> AH5269BK	•	•
			Safety grip angled body	0.33-0.66" (8.3-16.7mm)	BK & W	<input type="checkbox"/> AH5266A	—	•	•
			Quick grip straight body	0.22-0.66" (5.6-16.7mm)	BK	<input type="checkbox"/> AH5965BK	<input type="checkbox"/> AH5969BK		•
			Quick grip straight body	0.22-0.66" (5.6-16.7mm)	Y	<input type="checkbox"/> AH5965Y	<input type="checkbox"/> AH5969Y		•
			Auto grip straight body	0.33-0.66" (8.3-16.7mm)	BK & W	<input type="checkbox"/> 5266N	<input type="checkbox"/> 5269N	•	•

Industrial grade flanged inlets & outlets



Rating A	V/AC	NEMA	Description	Color	Inlet catalog no.	Outlet catalog no.	
15	125	5-15	Nylon construction, back wire	BK & W	<input type="checkbox"/> AH5278C [†]	<input type="checkbox"/> AH5279C*	•
			Metal shell, back wire	Steel	<input type="checkbox"/> AH5278 [‡]	<input type="checkbox"/> AH5246	•

* UL and CSA Listed, [†] Fed Spec certified, [‡]Only NOM spec

Industrial grade dimensional information: B-16, B-17

Specification information:

Safety grip industrial plugs & connectors: B-24
Quick grip plugs & connectors: B-24
Auto grip industrial plugs & connectors: B-24
Industrial flanged inlets & Flanged outlets: B-25

Color information:

BK (Black), W (White), Y (Yellow)



Compliances, specifications and availability are subject to change without notice.

Indicates NAFTA compliant - Page Q-32

RoHS compliant - Page Q-32