

Eaton 5269NHG

Catalog Number: 5269NHG

Eaton Arrow Hart auto grip hospital grade straight blade plug, #18-12 AWG, 15A, Industrial, 125V, Back wire, Black and white, Brass, Nylon, 5-15R, Two-pole, three-wire, grounding, Screw, Nylon, Core pack

General specifications



Product Name

Eaton Arrow Hart auto grip hospital grade straight blade plug

Catalog Number

5269NHG

UPC

040893120256

Product Length/Depth

1.91 in

Product Height

4.13 in

Product Width

1.78 in

Product Weight

0.207 lb

Warranty

Refer to warranty document.

Certifications

UL

NOM

Federal Specification Classification 622102

Product specifications

Device type

Connector

Color

White

Black

Face/body material

Nylon

Wiring method

Back wire

Material

Nylon

Allowable wire size

#18-12 AWG

Amperage Rating

15A

Number Of Poles

Two-pole

Contact material

Brass

Type

Connector

Device grade

Extra heavy-duty hospital grade

NEMA configuration

5-15R

Style type

Straight body

Design type

Straight blade

Connection type

Screw

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - 5269NHG](#)

Voltage rating

125V

Application

Industrial

Torque rating

14 lbf-inch

Packaging type

Core pack



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)