

# Eaton 5270W-BU

Catalog Number: 5270W-BU

Eaton residential grade duplex receptacle, #10 AWG, 15A, Residential, Flush, 125V, Side wire, White, Brass, Thermoplastic, 5-15R, Duplex, Screw, Thermoplastic

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton residential grade duplex receptacle	5270W-BU
	UPC
	032664752186
<b>Product Length/Depth</b>	<b>Product Height</b>
1.31 in	4.19 in
<b>Product Width</b>	<b>Product Weight</b>
0.69 in	0.15 lb
<b>Warranty</b>	<b>Certifications</b>
Refer to warranty document.	UL
	NOM
	Federal Specification Classification 6235
	01

## Product specifications

### Device type

Receptacle

### Color

White

### Face/body material

Thermoplastic

### Wiring method

Side wire

### Features

Copper and aluminum wire

### Material

Thermoplastic

### Mounting method

Flush

### Allowable wire size

#10 AWG

### Amperage Rating

15A

### Number Of Poles

Two-pole

### Contact material

Brass

### Type

Duplex receptacle

### Device grade

Standard grade

### NEMA configuration

5-15R

### Style type

Copal

### Design type

Straight blade

### Connection type

Screw

### Number of wires

## Resources

### Catalogs

[Residential Buyers Guide Section B](#)

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - 5270W-BU](#)

3

Receptacle type

Duplex

Voltage rating

125V

Application

Residential

Torque rating

14 lbf-inch



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)