

Heavy-Duty Spec Grade Single Receptacles, Side Wire, 20A, 125V, Light Almond

5351LA



Heavy-Duty Spec Grade Single Receptacle
Side Wire 20amp 125volt Light Almond



features & benefits

- Auto-ground clip assures positive ground.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.
- Backed-out tr-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility.
- One-piece brass triple-wire power contacts for lasting retention.

specifications

General Info

Color: light almond
Type: Single, Receptacles
Duty: Heavy Duty
Special Features: Side Wire

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No. 42
CSA Standard: Yes
Federal Spec: No
UL Listing No: UL498
UL Standard: Yes

UN SPS C: 39121406

UR: No

Dimensions

Depth U S: 1.08"

Height U S: 3.28"

Width U S: 1.32"

Technical Information

Amps: 20 Amp

Volts: 125V

Volts A C: 125

Capacity: Single

Grade Type: Federal Specification

Buy American Act Compliance

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant