



## HEAVY-DUTY SPEC GRADE SINGLE RECEPTACLES, SIDE WIRE, 20A, 125V, LIGHT ALMOND

5351LA | Pass & Seymour

#### **FEATURES & BENEFITS**

Heavy-Duty Spec Grade Single Receptacle Side Wire 20amp 125volt Light Almond

- · Auto-ground clip assures positive ground.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.
- · Backed-out tr-drive steel terminal screws. Internal screw-pressure-plate side wire capability.
- One-piece brass triple-wire power contacts for lasting retention.
- For covering patents, see www.legrand.us/patents.

#### **SPECIFICATIONS**

#### **GENERAL INFO**

Color: Light Almond Type: Single Receptacles

Duty: Heavy Duty

Special Features: Side Wire

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes Federal Spec: No UL Listing No: UL498 UL Standard: Yes UN SPSC: 39121406

UR: No

### **DIMENSIONS**

Depth (US): 1.08" Height (US): 3.28" Width (US): 1.32"

### **TECHNICAL INFORMATION**

Amps: 20A

Volts: 125V Volts (AC): 125 Capacity: Single

Grade Type: Federal Specification

# **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO Buy American Act Status: Trade Agreement Act Compliant

