



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 5361I Recp SGL 20A 125V S+B Wire Iv

*Pass & Seymour/Legrand*

Catalog Number	5361I
Manufacturer	Pass & Seymour/Legrand
Description	Heavy-Duty Spec Grade Single Receptacle, Back and Side Wire, 20A 125V
Weight per unit	0.1830 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
Number of Wires	3
Outlet Type	Indoor, Commercial
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

### Material, Color, and Finish

Color	Ivory
-------	-------

### Dimensions and Weight

Height	3.68
Width	1.093

### Descriptions

Description	RECP SGL 20A 125V S+B WIRE IV
extra long description	P&S 5361I RECP SGL 20A 125V S+B WIR
Long Description	Heavy-Duty Spec Grade Single Receptacle, Back and Side Wire, 20A 125V
Product Type	Recp SGL 20A 125V S+B Wire Iv
Special Features	Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly. One-piece brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face and thermoplastic back body. Internal screw-pressure-plate back wire capable of accepting #14 - #10 AWG solid or stranded copper or copper-clad wire. Terminal compartments isolated from each other for pos



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007536119
Manufacturers Part Number	53611
UPC	785007536119

## Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	100
Weight Per each	0.183

## Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	CUL, FEDSPEC, UL498, CSA C22.2 No. 42
Temperature Rating	-40° - 60° C