

Eaton 5366N

Catalog Number: 5366N

Eaton Arrow Hart auto grip straight blade plug, #16-12 AWG, 20A, Industrial, 125V, Back wire, Black and white, Brass, Nylon, 5-20P, Two-pole, three-wire, grounding, Screw, Nylon, Core pack

General specifications



Product Name	Catalog Number
Eaton Arrow Hart auto grip straight blade plug	5366N
	UPC
	040893018058
Product Length/Depth	Product Height
1.91 in	4.13 in
Product Width	Product Weight
1.78 in	0.207 lb
Warranty	Compliances
Refer to warranty document.	RoHS Compliant

Certifications

UL

NOM

Federal Specification Classification 6221

02

Product specifications

Device type

Plug

Color

Black

White

Face/body material

Nylon

Wiring method

Back wire

Material

Nylon

Allowable wire size

#16-12 AWG

Amperage Rating

20A

Number Of Poles

Two-pole

Contact material

Brass

Type

Plug

Device grade

Extra heavy-duty industrial specification grade

NEMA configuration

5-20P

Style type

Straight body

Design type

Straight blade

Connection type

Screw

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Resources

Brochures

Wiring Devices Buyer's Guide

Multimedia

Arrow Hart - Connecting Safety to Reliability since 1890

Specifications and datasheets

Eaton Specification Sheet - 5366N

Voltage rating

125V

Application

Industrial

Torque rating

14 lbf-inch

Packaging type

Core pack



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia