



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



5369X Straight Blade Conn 3W 20a125v

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 5369X |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Straight Blade Connector 2-Pole 3-Wire 20A 125a |
| Weight per unit | 0.1700 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|----------------|
| amperage rating | 20 |
| connection | Wire Grounding |
| Material | Nylon |
| Number of Wires | 3 |
| Poles | 2 |
| Voltage Rating | 125 |
| Wire Size | 4 |

Material, Color, and Finish

| | |
|-------|-------------|
| Color | Black&White |
|-------|-------------|

Dimensions and Weight

| | |
|------|--------|
| Size | 2.8 in |
|------|--------|

Descriptions

| | |
|------------------------|--|
| Description | STRAIGHT BLADE CONN 3W 20A125V |
| extra long description | P&S PS5369X STR BLD CONN 3W 20A125V |
| Long Description | Straight Blade Connector 2-Pole 3-Wire 20A 125A |
| Product Type | STR BLD Conn 3W 20a125v |
| Special Features | Ready to wire, rugged 2pc cord grip & internal dust shield |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007237030 |
| Manufacturers Part Number | PS5369X |
| UPC | 785007237030 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | Industrial cord connectors |
| Type | Straight Blade Connector |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.17 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|----------------|
| Application | Extra Hard Use |
| nema rating | 5-20R |
| standard | UL 498 |