



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 538722 1/2" Dual Speed Hammer-Drill Kit

*Milwaukee Electric Tool*

Catalog Number	538722
Manufacturer	Milwaukee Electric Tool
Description	Choose The Hammer Drill With Power and Speed Controls For Unmatched Versatility. The Adaptable 1/2 In. Dual-Speed Hammer Drill Features An 8.5 Amp Motor That Provides Overload Protection, Even When Drilling 3/4 In. Holes In Concrete. Choose Controls In Two Ranges: 0-1, 000 RPM/0-16, 000 BPM or 0-2, 500 RPM/0-40, 000. It'S Versatile Enough to Drill In Wood With Flat Boring Bits, Hole Saws, Auger Bits and Selfeed Bits – or Drill In Steel With Twist Bits and In Concrete With Percussion Bits. The Removable Side
Weight per unit	12.8 (lbs/each)
Product Category	Power Tools - Corded

### Features

amperage rating	8.5
-----------------	-----

### Descriptions

Description	1/2" DUAL SPEED HAMMER-DRILL KIT
extra long description	MILW 5387-22 1/2"8.5AHmmrDrillKit
Features	1/2 in. Dual Speed Hammer Drill Kit w/ Case
Long Description	Choose the hammer drill with power and speed controls for unmatched versatility. The adaptable 1/2 in. dual-speed hammer drill features an 8.5 amp motor that provides overload protection, even when drilling 3/4 in. holes in concrete. Choose controls in two ranges: 0-1, 000 RPM/0-16,000 bpm or 0-2, 500 RPM/0-40,000. It's versatile enough to drill in wood with flat boring bits, hole saws, auger bits and Selfeed bits – or drill in steel with twist bits and in concrete with percussion bits. The removable side
Product Type	1/2"8.5ahmmrdrillkit
Short Description	1/2"85AHmmrDrillKt
Special Features	8.5 AMP Motor Provides Overload Protection; Metal Gear Case Can Withstand Daily Jobsite Abuse; Light Weight Balanced Design Reduces Operator Fatigue; Dual Speed Motor Optimized For Concrete Fastening: 1-1,000 RPM, 0-16,000 BPM; 0-2,500 RPM, 0-40,000 BPM; Bpm: 0 - 16000/0 - 40000 BPM At No Load; Chuck Type: Keyed; Selfeed Bit Capacity: 2 IN; Cord Type: 10 FT Quik-Lok; Trigger Lock: No; Capacity In Steel: 1/2 IN; Capacity In Concrete: 3/4 IN; Tool Weight: 6.400 LB; Includes: Depth Gauge, Side Handle, Ch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Milwaukee®
GTIN	00045242025343
Manufacturers Part Number	538722
UPC	045242025343

## Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
Type	Dual Speed

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Weight Per each	12.8

## Uses, Certifications, and Standards

Application	For Drilling In Wood With Flat Boring Bits, Hole Saws, Auger Bits, And Selffeed Bits, It Can Also Be Used To Drill In Steel With Twist Bits And In Concrete With Percussion Bits
-------------	--