





Industrial grade plugs & connectors

Industrial grade plugs & connectors quick reference guide

AMP	V/AC	NEMA	Grip	Special	Body	Color	Page	Plug	Connector
15	125	 5-15P	ULTRA		STR	BK & W	B-10	AH5266	AH5269
					STR	BK	B-10	AH5266BK	AH5269BK
				HG	STR	BK & W	B-8	AH8215HG	AH8219HG
			SAFETY		ANG	BK & W	B-10	AH5266A	—
				HG	ANG	BK & W	B-8	AH8215HGA	—
				HG	ANG	C	B-8	AH8215HGAC	—
		HG		STR	C	B-8	AH8215HGC	AH8219HGC	
		QUICK		STR	BK	B-10	AH5965BK	AH5969BK	
				STR	Y	B-10	AH5965Y	AH5969Y	
			HG	STR	W	B-8	AH8115W	AH8119W	
		AUTO		STR	BK & W	B-10	5266N	5269N	
			HG	STR	BK & W	B-8	5266NHG	5269NHG	
HG	STR		RN	B-8	IG5266NHG	—			
20	125	 5-20P	ULTRA		STR	BK & W	B-11	AH5366	AH5369
				HG	STR	BK & W	B-8	AH8315HG	AH8319HG
			SAFETY	HG	ANG	BK & W	B-8	AH8315HGA	—
		HG		ANG	C	B-8	AH8315HGAC	—	
		QUICK		STR	BK	B-11	AH5364BK	AH5369BK	
			HG	STR	Y	B-11	AH5364Y	AH5369Y	
	HG	STR	BK & W	B-8	5366NHG	5369NHG			
15	250	 6-15P	ULTRA		STR	BK & W	B-11	AH5666	AH5669
			SAFETY	HG	ANG	BK & W	B-9	AH8225HGA	—
				HG	ANG	C	B-9	AH8225HGAC	—
		QUICK		STR	BK	B-11	AH5666BK	AH5669BK	
				STR	Y	B-11	AH5666Y	AH5669Y	
		AUTO		STR	BK & W	B-11	5666N	5669N	
20	250	 6-20P	ULTRA		STR	BK & W	B-12	AH5466	AH5469
			SAFETY	HG	ANG	BK & W	B-9	AH8325HGA	—
				HG	ANG	C	B-9	AH8325HGAC	—
		QUICK		STR	BK	B-12	AH5464BK	AH5469BK	
				STR	Y	B-12	AH5464Y	AH5469Y	
		AUTO		STR	BK & W	B-12	5466N	5469N	

 Hospital Grade








AMP	V/AC	NEMA	Color	Page	Flanged Inlet	Flanged Outlet
15	125	15-May	BK & W	B-10	AH5278C	AH5279C
			STEEL	B-10	AH5278	AH5246
20	125	20-May	BK & W	B-11	AH5778C	AH5779C
15	250	15-Jun	BK & W	B-11	AH5678C	AH5679C
20	250	20-Jun	BK & W	B-12	5878C	5879C


Compliances, specifications and availability are subject to change without notice.

www.eaton.com
www.eaton.com/arrowhart

Industrial grade plugs & connectors

Industrial grade plugs & connectors quick reference guide

AMP	V/AC	NEMA	Grip	Special	Body	Color	Page	Plug	Connector	
15	125	 5-15P	ULTRA		STR	BK & W	B-10	AH5266	AH5269	
					STR	BK	B-10	AH5266BK	AH5269BK	
				HG	STR	BK & W	B-8	AH8215HG	AH8219HG	
			 5-15R	SAFETY		ANG	BK & W	B-10	AH5266A	—
					HG	ANG	BK & W	B-8	AH8215HGA	—
					HG	ANG	C	B-8	AH8215HGAC	—
		HG			STR	C	B-8	AH8215HGC	AH8219HGC	
		QUICK		STR	BK	B-10	AH5965BK	AH5969BK		
				STR	Y	B-10	AH5965Y	AH5969Y		
			HG	STR	W	B-8	AH8115W	AH8119W		
		AUTO		STR	BK & W	B-10	5266N	5269N		
			HG	STR	BK & W	B-8	5266NHG	5269NHG		
HG	STR		RN	B-8	IG5266NHG	—				
20	125	 5-20P	ULTRA		STR	BK & W	B-11	AH5366	AH5369	
				HG	STR	BK & W	B-8	AH8315HG	AH8319HG	
			SAFETY	HG	ANG	BK & W	B-8	AH8315HGA	—	
				HG	ANG	C	B-8	AH8315HGAC	—	
		 5-20R	QUICK		STR	BK	B-11	AH5364BK	AH5369BK	
					STR	Y	B-11	AH5364Y	AH5369Y	
			AUTO	HG	STR	BK & W	B-8	5366NHG	5369NHG	
15	250	 6-15P	ULTRA		STR	BK & W	B-11	AH5666	AH5669	
			SAFETY	HG	ANG	BK & W	B-9	AH8225HGA	—	
				HG	ANG	C	B-9	AH8225HGAC	—	
			QUICK		STR	BK	B-11	AH5666BK	AH5669BK	
				STR	Y	B-11	AH5666Y	AH5669Y		
		AUTO		STR	BK & W	B-11	5666N	5669N		
		 6-15R	ULTRA		STR	BK & W	B-12	AH5466	AH5469	
				SAFETY	HG	ANG	BK & W	B-9	AH8325HGA	—
HG	ANG				C	B-9	AH8325HGAC	—		
QUICK				STR	BK	B-12	AH5464BK	AH5469BK		
		STR	Y	B-12	AH5464Y	AH5469Y				
 6-20R	AUTO		STR	BK & W	B-12	5466N	5469N			

 Hospital Grade

AMP	V/AC	NEMA	Color	Page	Flanged Inlet	Flanged Outlet
15	125	15-May	BK & W	B-10	AH5278C	AH5279C
			STEEL	B-10	AH5278	AH5246
20	125	20-May	BK & W	B-11	AH5778C	AH5779C
15	250	15-Jun	BK & W	B-11	AH5678C	AH5679C
20	250	20-Jun	BK & W	B-12	5878C	5879C

Compliances, specifications and availability are subject to change without notice.

www.eaton.com
www.eaton.com/arrowhart