



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2255 Northwest Parkway SE
30067-0000, GA Marietta
Phone: 678-398-4904
Fax: 678-398-4905



5651W SGL Recp 15A 250V S-Wire WH

Pass & Seymour/Legrand

Catalog Number	5651W
Manufacturer	Pass & Seymour/Legrand
Description	Heavy-Duty Spec Grade Single Receptacle Side Wire 15A 250V
Weight per unit	0.1636 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
Number of Wires	3
Outlet Type	Commercial, Indoor
Poles	2
Voltage	250.0 V
Voltage Rating	250
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Height	3.68
Width	1.08

Descriptions

Description	SGL RECP 15A 250V S-WIRE WH
extra long description	P&S 5651W SGL RECP 15A 250V S-WIRE
Long Description	Heavy-Duty Spec Grade Single Receptacle Side Wire 15A 250V
Product Type	SGL Recp 15A 250V S-Wire WH
Special Features	Auto-ground clip assures positive ground. Two drive screws anchor strap to back body and face where abrupt removal torque is greatest. Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength. Backed-out tri-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility. One-piece brass triple-wire power contacts for lasting retention.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2255 Northwest Parkway SE
30067-0000, GA Marietta
Phone: 678-398-4904
Fax: 678-398-4905

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007565133
Manufacturers Part Number	5651-W
UPC	785007565133

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.1636

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	6-15R
standard	CULUS, UL498, CSA C22.2 No. 42