

# Specifications

## Eaton 5669N

Eaton Arrow Hart auto grip straight blade connector,#18-12

AWG,15A,Industrial,250V,Back wire,Black and white,Brass,Polycarbonate with thermoplastic housing,6-15R,Two-pole,three-wire,grounding,Screw,0.33-0.66",Nylon,Core pack

### General specifications

<b>PRODUCT NAME</b>	Eaton Arrow Hart auto grip straight blade connector
<b>CATALOG NUMBER</b>	5669N
<b>UPC</b>	040893021607
<b>PRODUCT LENGTH/DEPTH</b>	1.91 in
<b>PRODUCT HEIGHT</b>	4.13 in
<b>PRODUCT WIDTH</b>	1.78 in
<b>PRODUCT WEIGHT</b>	0.181 lb
<b>CERTIFICATIONS</b>	UL NOM Federal Specification Classification 6221 02
<b>PRODUCT TYPE</b>	Auto grip



Powering Business Worldwide

## Product specifications

<b>DEVICE TYPE</b>	Connector
<b>TYPE</b>	Connector
<b>AMPERAGE RATING</b>	15A
<b>VOLTAGE RATING</b>	250V
<b>CONTACT MATERIAL</b>	Brass
<b>APPLICATION</b>	Industrial
<b>DEVICE GRADE</b>	Extra heavy-duty industrial specification grade
<b>WIRING METHOD</b>	Back wire
<b>NUMBER OF WIRES</b>	3
<b>NUMBER OF POLES</b>	Two-pole
<b>STYLE TYPE</b>	Straight body
<b>CORD RANGE</b>	0.33-0.66" in diameter
<b>MATERIAL</b>	Nylon
<b>PACKAGING TYPE</b>	Core pack
<b>COLOR</b>	White Black
<b>CONNECTION TYPE</b>	Screw
<b>ALLOWABLE WIRE SIZE</b>	#18-12 AWG
<b>NEMA CONFIGURATION</b>	6-15R
<b>TORQUE RATING</b>	14 lbf-inch
<b>DESIGN TYPE</b>	Straight blade
<b>FACE/BODY MATERIAL</b>	Polycarbonate with thermoplastic housing
<b>RECEPTACLE TYPE</b>	Two-pole, three-wire, grounding

## Resources

MULTIMEDIA	<a href="#">Arrow Hart - Connecting Safety to Reliability since 1890</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - 5669N</a> <a href="#">Arrow Hart industrial grade straight blade and locking devices brochure</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

