



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



58511 SGL Recp 20A 250V S-Wire Iv

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 58511 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Straight Blade Receptacle, 20 A, 250 V Ac, 2 Poles, 3 Wires, Back Wire Connection, Wall Mount, 1.380 In Length, 1.08 In Width, 3.28 In Height, Thermoplastic, Ivory, Corrosion Resistant, 0.1600 LB |
| Weight per unit | 0.1604 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|-----------------|--------------------|
| amperage rating | 20 |
| connection | Wire Ground |
| indoor/outdoor | Indoor |
| Outlet Type | Commercial, Indoor |
| Poles | Double Pole |
| Voltage | 250.0 V |
| Wire Size | 4 |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|------------------------------------|
| Description | SGL RECP 20A 250V S-WIRE IV |
| extra long description | P&S 58511 RECP SGL 20A 250V S-WIRE |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007585117 |
| Manufacturers Part Number | 58511 |
| UPC | 785007585117 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | Industrial receptacles |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 100 |
| Weight Per each | 0.1604 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|----------|---------------|
| Mounting | WALL |
| standard | CULUS, UL 498 |