

# MaxGrip M3 Plug, Yellow

PS5965Y



Straight Blade Plug 2pole 3wire 15amp  
125v



## features & benefits

- Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements; arc resistance exceeds UL requirements.
- Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws; close hinge housing around cord and tighten housing screws.
- Enclosed terminals provide solid, internally-clamped connections.
- Molded finger grips promote safe, sure handling.
- High-visibility yellow and orange, or gray.
- Hospital Grade version displays the Hospital Grade green dot.

## specifications

### General Info

Color: Yellow  
Product Series: MaxGrip  
Type: Plug

### Listing Agencies/Third Party Information

CSA Listing Info: Yes  
cULus: Yes  
cURus: No  
Federal Spec: No

UL Listing No: Yes  
UN SPS C: 39121402  
UR: No

**Dimensions**

Height U S: 1.83"  
Width U S: 1.34"

**Technical Information**

Amps: 15 Amp  
Volts: 125V  
Volts A C: 125

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant