



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 60512 #4 Compress. Butt Splice

*Abb Installation Products, Inc*

|                  |   |
|------------------|---|
| Catalog Number   | 60512   |
| Manufacturer     | Abb Installation Products, Inc  |
| Description      | Butt Splice Connector, #4 Awg Conductor Size, Non-Insulated, Aluminum/Copper Conductor Material, Green (Code) Insulation Color, +90 °C Operating Temperature, 1.81 In Overall Length, Compression Terminal, 35 KV, 0.03 LB/Ea |
| Weight per unit  | 0.0290 (lbs/each)   |
| Product Category | Large Terminals & Connectors  |

### Features

|                |          |
|----------------|----------|
| Material       | Aluminum |
| Voltage Rating | 35 kV    |

### Material, Color, and Finish

|        |            |
|--------|------------|
| Color  | Green      |
| Finish | Tin-Plated |

### Descriptions

|                        |                                    |
|------------------------|------------------------------------|
| Description            | #4 COMPRESS. BUTT SPLICE           |
| extra long description | ABB 60512 COMPRESSION CONNECTOR, 2 |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | COLOR-KEYED    |
| GTIN  | 00786210605128 |
| UPC   | 786210605128   |

### Taxonomies, Classifications, and Categories

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type                 | Aluminum Splice                   |

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 10    |
| Package         | 100   |
| Weight Per each | 0.029 |

### Uses, Certifications, and Standards

|                    |          |
|--------------------|----------|
| standard           | UL E9809 |
| Temperature Rating | 90 C     |