



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



60581 Knit Dipped Gloves, Cut Level A1, Touchscreen, Lar

Klein Tools

| | |
|------------------|--|
| Catalog Number | 60581 |
| Manufacturer | Klein Tools |
| Description | Knit Dipped Gloves, Cut Level A1, Touchscreen, Large, 2-Pair |
| Weight per unit | 0.1900 (lbs/each) |
| Product Category | Tools & Testers |

Features

| | |
|-----------------|---------------|
| gender | Unisex |
| Material | Nylon-Spandex |
| media | Yes |
| Overall Height | 2" (5.1 cm) |
| Overall Width | 3" (7.6 cm) |
| Water Resistant | NO |

Material, Color, and Finish

| | |
|-------|--------------|
| Color | Orange/Black |
|-------|--------------|

Dimensions and Weight

| | |
|----------------|---------------|
| Overall Length | 10" (25.4 cm) |
| Size | Large |
| Thickness | 1.5" (3.8 cm) |

Descriptions

| | |
|------------------------|--|
| Description | KNIT DIPPED GLOVES, CUT LEVEL A1, TOUCHSCREEN, LAR |
| extra long description | KLEIN 60581 A1 Cut Knit Dipped Glov |
| Long Description | Knit Dipped Gloves, Cut Level A1, Touchscreen, Large, 2-Pair |
| Product Type | A1 Cut Knit Dipped Gloves, L, 2-PR |
| Special Features | Touchscreen Capable Fingertips |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Klein Tools |
| GTIN | 00092644605819 |
| Manufacturers Part Number | 60581 |
| UPC | 092644605819 |

Taxonomies, Classifications, and Categories

| | |
|------|-------------|
| Type | Knit Dipped |
|------|-------------|

Packaging

| | |
|-----------------|----------------|
| Carton | 1 |
| Package | 10 |
| Weight | 4.8 oz (136 g) |
| Weight Per each | 0.19 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application
standard

Wet; Dry; Oily Conditions
ANSI A1 Cut Resistance