

Bulb Shape	Base	Watts	Order Code	Description	Volts	Case Qty	Filament Design	MOL (in)	LCL (in)	Rated Life (hrs)	Lumens Initial	Color Temp K	CBCP	Beam Spread	Warning and Caution Notices	Reduced Wattage	Additional Information
Decorative (continued)																	
40 Watts (continued)																	
G16.5	Med	40	31109	40GM/CL-PQ2/6	120	30	CC-2V	3.00		1500					5e, 9d		Clear, Globe, Medium Base, BDTH
		40	31110	40GM/W-PQ2/6	120	30	CC-2V	3.00		1500					5e, 9d		White, Globe, Medium Base, BDTH
G25	Med	40	12979	40G25/W 6PK	120	6	CC-6	4.50		1500							White, Globe
		40	12980	40G25 6PK	120	6	CC-6	4.50		1500							Clear, Globe
		40	48694	40G25C/RVL PQ1/6	120	6	CC-6	4.50		1500							Reveal®
G40	Med	40	48695	40G25W/RVL PQ1/6	120	6	CC-6	4.50		1500							Reveal®
		40	36191	40G40/W 6PK	120	6	CC-6	6.93		2500							White, Globe
60 Watts																	
B10	Cand	60	27298	60BC/CD4	120	30	CC-2V	3.75		1500							Clear, Blunt Tip
		60	74036	60BC/RVL/CF-T4/6	120	6	C-7A	3.75		1500							Reveal® Clear, Ceiling Fan, Blunt Tip
B13	Med	60	27497	60BM/CD4	120	6	C-9	4.62		1500							Clear, Blunt Tip
		60	72781	60BM/RVL/CD2-4PK	120	4	C-9	4.62		1500					2c, 9i		Reveal®, Blunt Tip
CA10	Med	60	21009	60CAM CARD4	120	30	CC-2V	4.56		1500							Clear, Bent Tip
CA10	Cand	60	15781	60CAC 25PK	120	200	CC-2V	4.12		1500							Clear, Bent Tip
		60	16050	60CAC CARD 4	120	30	CC-2V	4.12		1500							Clear, Bent Tip
		60	16051	60CAC/F CARD4	120	30	CC-2V	4.12		1500							Frost, Bent Tip
G16.5	Cand	60	72777	60GC/CD2-4PK	120	4	CC-2V	3.00		1500					5e, 9d		Clear, Globe
G16.5	Cand	60	44723	60GC/W PQ2/6	120	30	CC-2V	3.00		1500					5e, 9d		White, Globe
G16.5	Med	60	31114	60GM/CL-PQ2/6	120	30	CC-2V	3.00		1500					5e, 9d		Clear, Globe, Medium Base, BDTH
		60	31115	60GM/W-PQ2/6	120	30	CC-2V	3.00		1500					5e, 9d		White, Globe, Medium Base, BDTH
G25	Med	60	42360	60G25C/RVL PQ1/6	120	6	CC-6	4.50		1500							Reveal®, Clear-Globe
		60	42361	60G25W/RVL PQ1/6	120	6	CC-6	4.50		1500							Reveal®, White - Globe
		60	14846	60G25 6PK	120	6	CC-6	4.50		1500							Clear, Globe
		60	14848	60G25/W 6PK	120	6	CC-6	4.50		1500							White - Globe
G30	Med	60	14850	60G30/W 6PK	120	24	CC-9	5.00		2500							White - Globe, Retail Pack
G40	Med	60	14187	60G40 6PK	120	6	CC-6	6.93		2500							Clear - Globe
		60	49780	60G40/W 6PK	120	6	CC-6	6.93		2500							White - Globe
75 Watts																	
E17	Med	75	73289	75E17/TF-4PK	120	4	CC-6	5.00		4000							
G40	Med	75	36193	75G40/W 6PK	120	6	CC-6	6.93		2500							White - Globe
100 Watts																	
F20	Med	100	44540	100F20/TF PQ1/6	120	30	CC-9	5.00		3000							Post Light, Teflon® Coated, Saf-T-Gard® BB
G40	Med	100	16742	100G40/W CPK	120	24	CC-6	6.93		2500							White - Globe
		100	49781	100G40/W 6PK	120	6	CC-6	6.93		2500							White - Globe
150 Watts																	
G40	Med	150	16585	150G40/W	120	24	CC-6	6.93		2500							White - Globe
Portable Lighting Products																	
R30	Med	65	44848	PLK 1 UNIT	120	4	CC-6	5.37		2000					2a, 5e, 9k		Plant Light Kit includes one 75R30/PL Plant Light lamp, UL listed holder and information booklet.