



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 61044100 1" Met L/T, Non UI 400' Afc Cable

Catalog Number	61044100
Manufacturer	Afc Cable
Description	Non-UI Liquid-Tuff™ Liquidtight Conduit, Type VF, 6100 Series, Liquidtight Flexible Metal Conduit. Zinc Coated Galvanized Low Carbon Steel, Flame Retardant PVC Jacket. Color: Gray, 1 Inch Diameter, 400 Foot Reel
Weight per unit	180.0 (lbs/each)
Product Category	Flexible Metallic Conduit

### Features

Inside Diameter	1.041/1.066
Material	Steel
outside diameter	1.290/1.315

### Material, Color, and Finish

Color	Gray
Finish	PVC
Jacket Material	PVC

### Dimensions and Weight

Length	400
--------	-----

### Descriptions

Description	1" MET L/T, NON UL 400'
extra long description	AFC 6104-41-00 1 LIQUID-TUFF VF LT
Features	LIQUID-TUFF™ Liquidtight, Flexible Steel Conduit, Type VF is a general purpose Non-UL raceway that is oil and sunlight resistant. Designed to be used for specific applications where Underwriters Laboratories Inc. (UL) or other agency approvals are not required.
Long Description	Non-UL LIQUID-TUFF™ Liquidtight Conduit, Type VF, 6100 Series, Liquidtight Flexible Metal Conduit. Zinc Coated Galvanized Low Carbon Steel, Flame Retardant PVC Jacket. Color: Gray, 1 inch Diameter, 400 Foot Reel
Product Type	1 Liquid-Tuff VF LT 400 RL
Short Description	1 LIQUID-TUFF VF LT 400 RL

### Manufacturer Information

Brand	Afc Cable
Manufacturers Part Number	6104-41-00



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	Liquidtight Flexible Metal Conduit

## Trade Size

Trade Size	1
------------	---

## Packaging

Carton	1
Weight	0.5
Weight Per each	180

## Uses, Certifications, and Standards

Application	600 V and lower circuits.
Temperature Rating	140