

Trident® Headlamp

Case Material: Water resistant lightweight thermoplastic construction. Yellow or Green.

Dimensions: Face Cap Diameter: 1.86 in. (4.72 cm)
 Maximum Width: 2.55 in. (6.48 cm)
 Maximum Depth: (Includes head strap mounting plate) 2.53 in. (6.42 cm)

Weight: 4.64 oz (131.54 grams)* Includes head strap mounting plate

Lens: Unbreakable polycarbonate lens.

Light Source: 3 Volt, 300 mA Xenon Bi-Pin Bulb or three 100,000 hour life LEDs.

Light Output: Xenon Bulb: 12 lumens measured system output.
 Yellow Model: One (1) White LED: 9 lumens measured system output.
 Three (3) White LEDs: 24 lumens measured system output.
 Green Model: One (1) Safety Green LED: 4 lumens measured system output.
 Two (2) White LEDs: 18 lumens measured system output.

On/Off: Push button sequences through (1) LED, (3) LEDs , (1) Xenon or Off.

Run Time: Up to 150 hours. (Single LED)

Battery: Three (3) "AAA" alkaline batteries.

- Features:
- (3) Lighting Modes
 - Rubber Hard Hat Strap (Included in purchase)
 - 90 degree tilting head
 - Water Resistant
 - Green model features (1) night vision safety green LED and (2) white LEDs; Night vision green LED won't spook game

Approvals: (Yellow only) UL Classified for Class I, Division 2
 (Yellow only) UL Classified to Canadian safety standards for Class I, Division 2
 Most Models Meet applicable European Community Directives.

Warranty: Limited lifetime warranty.

*With batteries (included in purchase).
 Made in China



Item		UPC	Part #
Trident with white LEDs	Yellow	080926-61050-7	61050
Trident with white LEDs UL Listed	Yellow	080926-61049-1	61049
Trident with (2) white LEDs, (1) Green LED	Green	080926-61051-4	61051
Battery Cartridge	(not shown)	080926-61001-9	61001



STREAMLIGHT

30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax • www.streamlight.com